



China model range

50 Hz range

Model name	Standby rating		Prime rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure
	kVA	kWe	kVA	kWe					
C150D5B	150	120	138	110	6BTAA5.9-15	UCI274E	PC 1.2	Unemissionized	Yes
C175D5B	175	140	160	128	6BTAA5.9-15	UCI274F	PC 1.2	Unemissionized	Yes
C220D5	220	176	200	160	6CTAA8.3-G7	UCI274H	PC 1.2	Tier 1	Yes
C250D5	250	200	227	182	6CTAA8.3-G9	UCDI274J	PC 1.2	Tier 1	Yes
C275D5B	275	220	250	200	6LTAA9.5-G3	UCDI274K	PC 1.2	Tier 1	Yes
C300D5B	300	240	275	220	6LTAA9.5-G3	HC4D	PC 1.2	Tier 1	Yes
C330D5B	330	264	300	240	6LTAA9.5-G1	HC4D	PC 1.2	Tier 1	Yes
C350D5B	350	280	320	256	6LTAA9.5-G1	HC4S	PC 1.2	Tier 1	Yes
C400D5EB	400	320	360	288	QSZ13-G7	HC5C	PC 2.2	Tier 1	Yes
C450D5EB	450	360	409	327	QSZ13-G7	HC5C	PC 2.2	Tier 1	Yes
C500D5	500	400	455	364	QSZ13-G5	HC5C	PC 2.2	Tier 1	Yes
C500D5E	500	400	455	364	QSX15-G8	HC5C	PC 3.3		Yes
C550D5E	550	440	500	400	QSZ15-G8	HC5D	PC 2.2	Tier 1	Yes
C640D5	640	512	582	466	KTA19-G6	HC5E	PC 1.1	Tier 1	No
C700D5	706	565	640	512	VTA28-G5	HC5F	PC 3.3	Tier 1	No
C825D5	825	660	750	600	QSK23-G3	S6L1C41	PC 3.3	Tier 1	Yes
C900D5	900	720	820	656	QSK23-G3	S6L1D41	PC 3.3	Tier 1	Yes
C1000D5	1041	833	939	751	QSK30-G3	S6L1DD4	PC 3.3	Tier 1	No
C1100D5B	1132	906	1029	823	KTA38-G14	S6L1DF41	PC 3.3	Tier 1	Yes
C1250D5A	1250	1000	1125	900	KTA38-G9	PI734A	PC 3.3	Tier 1	No
C1400D5	1400	1120	1250	1000	KTA50-G3	PI7348	PC 3.3	Tier 1	No
C2250D5	2250	1800	2000	1600	QSK60-G4	PI734G	PC 3.3	Tier 1	No
C2500D5A	2500	2000	2250	1800	QSK60-G8	LVS1804R	PC 3.3	Tier 1	No

*Specifications may change without notice