

North America model range



60 Hz range

Model name	Fuel type	Standby rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure
		kVA	kWe					
C13N6H	NG/P	13	13	QSJ999G		Stealth controller	EPA NSPS	Yes
C17N6H	NG/P	17	17	QSJ999G		Stealth controller	EPA NSPS	Yes
C20N6H	NG	18	18	QSJ999G		Stealth controller	EPA NSPS	Yes
C20N6H	P	20	20	QSJ999G		Stealth controller	EPA NSPS	Yes
C20N6	NG/P	25	20	QSJ2.4G	CA115	PC 1.1	EPA NSPS	Yes
C25N6	NG/P	31	25	QSJ2.4G	CA115	PC 1.1	EPA NSPS	Yes
C30N6	NG/P	38	30	QSJ2.4G	CA115	PC 1.1	EPA NSPS	Yes
C36N6	NG/P	45	36	QSJ2.4G	CA115/CA125	PC 1.1	EPA NSPS	Yes
C40N6	NG/P	50	40	QSJ2.4G	CA115/CA125	PC 1.1	EPA NSPS	Yes
C45N6	NG/P	56	45	QSJ5.9G-G1	UC2D/UC2E/UC2F	PC 1.1; PC 2.3	EPA NSPS	Yes
C50N6	NG/P	63	50	QSJ5.9G-G1	UC2D/UC2E/UC2F	PC 1.1; PC 2.3	EPA NSPS	Yes
C60N6	NG/P	75	60	QSJ5.9G-G2	UC2E/UC2F/UC2G/UC3D	PC 1.1; PC 2.3	EPA NSPS	Yes
C70N6	NG/P	88	70	QSJ5.9G-G3	UC2F; UC2G; UC3C; UC3D	PC 1.1; PC 2.3	EPA NSPS	Yes
C80N6	NG/P	100	80	QSJ5.9G-G3	UC2G; UC3E; UC3C; UC3D	PC 1.1; PC 2.3	EPA NSPS	Yes
C100N6	NG/P	125	100	QSJ5.9G-G3	UC3D; UC3E; UC3F	PC 1.1; PC 2.3	EPA NSPS	
C125N6	NG/P	156	125	QSJ8.9G	UC3D; UC3E; UC3H; UC3F	PC 2.3	EPA NSPS	Yes
C150N6	NG/P	188	150	QSJ8.9G	UC3E; UC3F; UC3G; UCD3J	PC 2.3	EPA NSPS	
C175N6B	NG	219	175	QSJ8.9G	UC3H; UC3G; UCD3J; UCDI274K	PC 2.3; PC 3.3	EPA NSPS	Yes
C200N6B	NG	250	200	QSJ8.9G	UCD3J; UCDI274K	PC 2.3; PC 3.3	EPA NSPS	Yes

* Specifications may change without notice