

# BLUEQUIP

## Single Skin Coolant & AdBlue® Tanks



### Standard Specification

- Single skin solution for bulk coolant and AdBlue® ideal for indoor applications or where tank is going into a bunded area.
- Lockable pump cabinet protects against unauthorised access, mechanical damage & extreme weather conditions.
- Very cost effective & adaptable for many different applications.
- Attractive shape & colour.
- All equipment spare parts to be stocked in Melbourne.
- AFLO provide service to our units Australia wide.
- Dimensions for 5,000L AdBlue® & Coolant Tanks: 2.0m (L) x 2.0m (W) x 2.05m (H)
- Dimensions for 10,000L AdBlue® & Coolant Tanks: 2.4m (L) x 2.4m (W) x 2.53m (H)
- Dimensions for 16,500L AdBlue® & Coolant Tanks: 3.1m (L) 3.1m (W) x 2.50m (H)
- Dimensions for 24,000L AdBlue® & Coolant Tanks: 3.5m (L) 3.5m (W) x 3.07m (H)

