

Cummins Repower™

With a factory-built and factory-backed engineered crate engine package from Cummins Repower, continuous improvement and support is what sets us apart from the used junkyard engines. Trust the heart of your build to the company who has a 24/7 support network and 99 years of unrivaled reputation as an independent diesel engine manufacturer. When reliability and efficiency matter most for your repower project, depend on a factory-built, genuine crate engine from Cummins.



Follow us on Instagram @cumminsrepowerofficial

On sale now at cumminsrepower.com | 1-800-CUMMINS | Columbus, Indiana (USA)

Bulletin 5410825 Rev. 5/18


R2.8 Turbo Diesel

Features/Specs

| Displacement | 2.8 L (171 cu in) |
|-------------------|------------------------------|
| Cylinders | 4 |
| Aspiration | Turbocharged and Aftercooled |
| Torque* | 267 lb-ft @1500-3000 RPM |
| Horsepower* | 161 hp @ 3600 RPM |
| Bore | 94 mm (3.70 in) |
| Stroke | 100 mm (3.94 in) |
| Compression Ratio | 16.9:1 |
| Fuel System | Bosch Electronic |
| Engine Weight | 503 lbs |

^{*}Final ratings may vary.





Engine images for marketing purposes only. Actual product may vary.

Wiring Harness & Controls

