



VALVOLINE CUMMINS PRODUCT CATALOGUE



**SPECIALISTS IN
HEAVY DUTY LUBRICANTS**



CUMMINS PRODUCT CATALOGUE



1. ENGINE OILS	4	4. GREASES	9
Premium Blue	4	Multipurpose	9
ProFleet	5	Specialty Greases	10
All-Fleet	5		
HD	6		
GEO	6		
2. DRIVELINE OILS	6	5. AGRI, CONSTRUCTION AND MARINE OILS	11
Valvoline ATF	6	Marine	11
Valvoline ATF PRO	6	S.T.O.U.	11
Gear Oil PRO	6	UTTO	11
Valvoline Gear Oil	7	Unitrac	11
Valvoline Total Drive Line	7		
Valvoline Total Drive Line PRO	7	6. INDUSTRIAL OILS	12
Axle Oil	7	EPG	12
Transmission	7	Compressor Oils	13
3. COOLANTS	8	7. HYDRAULIC OILS	14
Advanced	8	Ultramax Extreme	14
HD Extended Life	8	Ultramax	14
HD Nitrite Free	8	Hydraulic	15
		Turbine Oils	16
		Compressor Oils	17
		Heat Transfer Oils	17
		Slideway Oils	17
		Circulation Oils	18



HD



HD 10W

API: CF

- GE Jenbacher Series 2, 3, 4 and 6; MWM (Deutz); Caterpillar CG gas engines
- Caterpillar 35XX & 36XX series engines; Guascor; MAN 3271-2; MTU series 4000; Perkins 4000 series; Rolls Royce KG1-4, BV-G & CR-G; Tedom; Wärtsilä 34SG & 50SG; Waukesha Cogen

20L	208L	1000L	BULK
VE12606	608865	VE12615	VE90188



HD 30

API: CF

- GE Jenbacher type 2, 3, 4 and 6. For sour gas applications, type class B and C

208L	1000L	BULK
VE12726	VE12738	VE12739

GEO



GEO SNG-6

- GE Jenbacher Series 2, 3, 4 B, C, D, 6 C, E, F, J ;
- Cummins; MTU; MWM (Caterpillar Energy Solutions); Wärtsilä; Waukesha; Suitable for use in: Cummins QSK60G Natural Gas fueled engines

208L	1000L	BULK
891716	-	891717



GEO SNG-4

ACEA E7, E9; API: CI-4, CI-4 plus, CJ-4/SM

- GE Jenbacher Series 2, 3, 4 and 6; MWM (Deutz); Caterpillar CG gas engines
- Caterpillar 35XX & 36XX series engines; Guascor; MAN 3271-2; MTU series 4000; Perkins 4000 series; Rolls Royce KG1-4, BV-G & CR-G; Tedom; Wärtsilä 34SG & 50SG; Waukesha Cogen

208L	1000L	BULK
885731	885690	885651



GEO PLUS LA 40

ACEA E7, E9; API: CI-4, CI-4 plus, CJ-4/SM

- GE Jenbacher type 2, 3, 4 and 6. For sour gas applications, type class B and C

208L	1000L	BULK
833832	833831	833610

2. DRIVELINE OILS

ATF



Heavy Duty ATF

- Voith H55.6336.xx
- ISO L-HA; GM Dextron IIIH; Ford MERCON V; GM Allison C-4 / TES-295; MAN 339 Type V2/Z2; MB 236.9; ZF TE ML 03D, 04D, 14B, 16L, 17C, 20B

20L	208L
897661	897662



Heavy Duty ATF D II

- Voith H55.6335.xx; ZF TE-ML 04D, 11A, 14A
- ISO L-HA; GM Dextron IID; GM Allison C-4; Ford MERCON; MB 236.6; MAN 339-D V1/Z1; Caterpillar TO-2

20L	208L
897663	897664

ATF PRO



Heavy Duty ATF PRO

- MAN 339 Type V1, Z1, L2 ; MB-Approval 236.1, Voith H55.633533 (former G 607); ZF TE-ML 04D, 14A (ZF001873)
- GM Dextron IID; Ford Mercon; Allison C-4; ZF TE-ML 03D, 05L, 09, 11A, 17C, 21L

12 X 1L (SW)	4 X 5L (SW)	20L	208L
868208	866915	866916	866918

GEAR OIL PRO



Heavy Duty Gear Oil PRO 75W-80

API: GL-4

- MAN 341 Type VR; MB-Approval 235.29; Volvo 97307
- EATON Manual Transmission; MAN 341 Type E4; Voith Retarder 153.00090010

20L	12 X 1L (SW)	20L	208L
866927	868210	866929	866930

GEAR OIL



Heavy Duty Gear Oil 75W-80

API: GL-4

12 X 1L (SW)	4 X 5L (SW)	20L	208L
868215	866950	868216	866951



Light & Heavy Duty Gear Oil 80W-90

API: GL-4

- ZF TE-ML 08, 24A

12 X 1L (SW)	20L	208L
868217	866956	866957



Heavy Duty Gear Oil 80W

API: SG

- JASO MA

208L
866954

TOTAL DRIVELINE



Heavy Duty TDL 75W-90

API: GL-4, GL-5, MT-1

- Mack GO-J; MAN 341 type Z2 (ZF); MAN 342 type M3 (Meritor); MIL-PRF-2105E; Scania ST0 1-0; ZF TE-ML 02B, 05A, 07A, 08, 12L, 12N, 16B, 17B, 19B, 21A

20L	208L	BULK
882024	882028	882029

TOTAL DRIVELINE PRO



Heavy Duty TDL PRO 75W-90

API: GL-4, GL-5, MT-1

- MAN 341 type Z2 (ZF); MAN 342 type S1; MB-Approval 235.8; SAE J2360; Scania ST0 1-0; Volvo 97312; ZF TE-ML 05A, 12L, 12N, 16F, 17B, 19C, 21A (ZF001283)
- Arvin Meritor Axles 0-76-N; Mack GO-J; MAN 341 type E3 (Eaton); MAN 342 type M3

12 X 1L (SW)	20L	60L	208L	1000L
868211	866932	866933	866934	868212

AXLE OIL



Heavy Duty Axle Oil 75W-90 Limited Slip

API: GL-5

20L	BULK
866948	866947



Heavy Duty Axle Oil 75W-140

API: GL-5, MT-1

- Scania ST0 1-0

20L	208L
879813	879814



Heavy Duty Axle Oil 85W-140

API: GL-5

- ZF TE-ML 07A, 08

20L	208L
866941	866942



Light & Heavy Duty Axle Oil 80W-90

API: GL-5

- ZF TE-ML 07A, 08

12 X 1L (SW)	4 X 5L (SW)	20L	208L
868214	866944	866945	866946

TRANSMISSION



DT Transmission Oil TO-4M DDT

API: GL-4

- Allison TES-439; Caterpillar TO-4M; ZF TE-ML 03C/ 07D/ 07F

20L	208L	1000L	BULK
888403	888402	888547	888401



DT Transmission Oil 10W

API: CF, MT-1

- Caterpillar TO-4; Allison C-4; ZF TE-ML 03C, 07F; Komatsu KES 07.868.1; Caterpillar TO-2 Eaton Fuller*; Dana*; Euclid*

20L	208L	BULK
819582	VE17818	682697



DT Transmission Oil 30

API: CF, MT-1

- Caterpillar TO-4; Allison C-4; ZF TE-ML 03C, 07F; Komatsu KES 07.868.1; Caterpillar TO-2 Eaton Fuller*; Dana*; Euclid*

20L	208L	BULK
756754	VE17838	680749

6. INDUSTRIAL OILS

EPG



EPG 68

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
897671	897673



EPG 100

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
890747	890746



EPG 220

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
890761	890750



EPG 460

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
897672	897674



EPG S68

● ISO 6743-6; ISO L-CKC/CKD/CKE; ISO 12925-1 CKC/CKD/CKE; DIN 51517/3 CLP; SIEMENS MD FLENDER GEARBOXES; AGMA 9005-E02; AIST 224; DAVID BROWN S1.53.101;

20L	208L
896756	896757



EPG 150

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
890749	890748



EPG 320

● AGMA 9005-F16; ISO 12925-1 CKC/CKD/CKE; Danielli 0.000.001 Rev 15 CKC; David Brown S1.53.101 Type E; DIN 51517-3; Fives Cincinnati EP Gear Oils; Flender GmbH; GM LS2 EP Gear Oils; RENK 36011-11 (2012); Schaeffler FAG Step 1 - 4; Schuler Pressem GmbH DT 55 005 Edition 1 (2013); SMS Group SN 180-3; U.S. Steel 224; ZF TE-ML 04H; ZF Witten ZFN-W-17-145

20L	208L
890763	890762



EPG S150

● AIST 224 (U. S. Steel 224); AGMA 9005-E02; DIN 51517 Part 3; ISO VG 150; ISO 12925-1

20L	208L
888585	888602

COMPRESSOR OILS



Compressor Oil 32

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891074	891066



Compressor Oil S46

● ISO L-DAB/DAG/DAH/DAJ; ISO 6743-3A; DIN 51506 VD-L

20L	208L
891076	891068



Compressor Oil 100

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891078	891070



Compressor Oil 220

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891080	891072



Compressor Oil 46

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891075	891067



Compressor Oil 68

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891077	891069



Compressor Oil 150

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891079	891071



Compressor Oil 320

● ISO L- DAB/DAG; ISO 6743-3A; DIN 51506 VD-L; DIN 51524/2; AFNOR NF E 48-603 HM; Eaton Vickers M-2950-S/ I-286-S

20L	208L
891081	891073



Valvoline Circulation Oil 100

● ISO L-HL; ISO 6743-4; ISO 11 158 (HL); DIN 51524 part 1 (HL)

20L	208L
891054	891046



Valvoline Circulation Oil 150

● ISO L-HL; ISO 6743-4; ISO 11 158 (HL); DIN 51524 part 1 (HL)

20L	208L
891055	891047



Valvoline Circulation Oil 220

● ISO L-HL; ISO 6743-4; ISO 11 158 (HL); DIN 51524 part 1 (HL)

20L	208L
891056	891048



Valvoline Circulation Oil ML 100

● ISO L-HL; ISO 6743-4; ISO 11158 (HL); DIN 51 517 deo 2 (CL); DIN 51 524 deo 1 (HL); MORGAN MORGOIL Lubricant Specification; New Oil; MORGAN MORGOIL Advanced Lubricant; New Oil; Danielli 0.000.001 rev.15

20L	208L
891057	891049



Valvoline Circulation Oil ML 220

● ISO L-HL; ISO 6743-4; ISO 11158 (HL); DIN 51 517 deo 2 (CL); DIN 51 524 deo 1 (HL); MORGAN MORGOIL Lubricant Specification; New Oil; MORGAN MORGOIL Advanced Lubricant; New Oil; Danielli 0.000.001 rev.15

20L	208L
891062	891050



Valvoline Circulation Oil ML 320

● ISO L-HL; ISO 6743-4; ISO 11158 (HL); DIN 51 517 deo 2 (CL); DIN 51 524 deo 1 (HL); MORGAN MORGOIL Lubricant Specification; New Oil; MORGAN MORGOIL Advanced Lubricant; New Oil; Danielli 0.000.001 rev.15

20L	208L
891064	891051



Valvoline Circulation Oil ML 460

● ISO L-HL; ISO 6743-4; ISO 11158 (HL); DIN 51 517 deo 2 (CL); DIN 51 524 deo 1 (HL); MORGAN MORGOIL Lubricant Specification; New Oil; MORGAN MORGOIL Advanced Lubricant; New Oil; Danielli 0.000.001 rev.15

20L	208L
891063	891052



Valvoline Circulation Oil S150

● ISO VG 150; FZG, DIN 51354: 12; Rust resistance test D 665 A & B: pass

20L	208L
882117	882163





Valvoline Europe

Wieldrechtseweg 39
3316 BG Dordrecht
The Netherlands

Tel: +31 (0)78 654 3500

www.valvolineurope.com

