



Cummins India Limited

Cummins India Office Campus, Tower A, 3rd Floor, Survey No.21, Balewadi, Pune - 411045 (MH)

Toll free No.:1-800-210-2525 Email ID: care.india@cummins.com



395mm & 430mm Dia Cover Assembly

Features	Advantage	Benefits	
Weight optimized Sheet Metal Cover	Improved heat absorption & reduced facing wear	Increased reliability	
Chrome Vanadium spring steel Diaphragm	High fatigue life of fingers	Better service life	
Induction hardened Boron steel ** Diaphragm spring holding rivets	Minimized Wear	Higher Durability	
Comes with Transit Clamp (Shipping Clip)	Eliminate straps buckling	Lesser transit damage	

^{**} For 395mm dia Clutch

395mm & 430mm Clutch Disc

Features	Advantage	Benefits
Co-axial Springs available	For Smooth transitioning	Smoother operation
Chrome Silicon Springs	higher fatigue life	Better durability
Torque at 80% Safety Factor	for smooth engagement & to eliminate Transmission Noise.	Lower noise
Thicker Drive Hub with high manganese toughened steel	Improved shock loading capacity	Better shock resistance with reduced gear rattle
Carbo-nitrided Back plates & Front plates	lower wear & stop window biting by spring	Higher reliability
Cushion Spring provided	Improved cushioning and Better Heat Dissipation	Lower driver fatigue
Robust Clutch Facing	High co-efficient of friction for better heat conductivity	Increase service life












Sr. No.	Cummins Part No.	Clutch Size (Diameter)	Application	
1	AX1016899	395	Clutch - Diaphragm Cover Assy 395 Dia TATA	
2	AX1016900	395	Clutch - Clutch Disc 395 Dia TATA with 1.75" Spline	
3	AX1016901	430	Clutch - Diaphragm Cover Assy 430 Dia TATA Prima	
4	AX1016902	430	Clutch - Clutch Disc 430 Dia TATA Prima with 2" Spline	
5	AX1016903	395	Clutch - Diaphragm Cover Assy 395 Dia Bharat Benz	
6	AX1016904	395	Clutch - Clutch Disc 395 Dia Bharat Benz 18 Teeth with 1.75" Spline	
7	AX1016905	430	Clutch - Clutch Disc 430 Dia Bharat Benz 18 Teeth with 1.75" Spline	
8	AX1016906	430	Clutch - Diaphragm Cover Assy 430 Dia Bharat Benz	
9	AX1016907	395	Clutch - Diaphragm Cover Assy 395 Dia Man Truck	
10	AX1016908	395	Clutch - Clutch Disc 395 Dia Man Truck with 1.5" Spline	
11	AX1016909	430	Clutch - Clutch Disc 430 Dia Man Truck 1.5" Spline	
12	AX1016910	430	Clutch - Diaphragm Cover Assy 430 Dia Man	
13	AX1015453	395	Clutch - Diaphragm Cover Assy 395 Dia Mahindra Navistar	
14	AX1015454	395	Clutch - Clutch Disc 395 Dia Mahindra Navistar 10 Teeth with 1.75" Spline	



Induction Hardened Fingers

SOFT ZONES FOR PARTS SQUEEZING (PROVIDES DEAD FULCRUM)

SOFT & TOUGH CORE


IND. HARDENING ZONE INNER AREA HARDNESS 40-52 HRC

Shipment Cup - Protect straps from damage during shipment.

Remain attached throughout the clutch life

- Helps in preventing oscillation.


- Helps in Pressure plate Lift.



Shipment Cup - Protect straps from damage during shipment.

Remain attached throughout the clutch life

- Helps in preventing oscillation.
- Helps in Pressure plate Lift.



Pre-damper spring - to damp out vibration to induce gear rattle.

