

ISL 490 Parts Info
FRONT HOUSING

Customer Part Number Cross Reference

Customer	Part Number
CUMMINS	3948274

Where Used Listing

Part	*	Qty	Desc
26308		1	<obs>HSG ASSY FRONT 12VDC PKGD
1024402		1	HSG ASSY FRONT 12VDC PKGD 490
5024402		1	HOUSING ASSY FRONT 12VDC BULK

Bill of Materials Listing

Part	*	Qty	Desc
1082		1	SEAL RING - CENTER
1083		1	SEAL RING - LOWER
7500		3	SPRING C/V INNER ORANGE
9922		2	DRIVE SCREW #4 X 1/4 LG
11251		3	COLLAR CONTROL VALVE
11259		1	SPRING CHECK VALVE STOP
11260		1	RETAINER SPRING CHECK VALVE
11261		1	RING RETAINER CHECK VALVE
11262		1	BALL 9/32 DIA GRADE 25
11283		3	SPOOL ASSY CONTROL VALVE
11284		3	RING RETAINER CONTROL VALVE
11395		3	NUT HEX JAM 1/2-20
11434		3	SPRING C/V OUTER WHITE
12983		1	PISTON ACCUMULATOR
12990		1	SPRING
12991		4	RING RETAINING
13500		3	RETAINER SPRING SLAVE PISTON
18209		3	SPRING INNER SLAVE PISTON
18485		13	PLUG PIPE FLUSH SEAL 1/16-27
18722		3	SPRING FLAT
18730		3	SCR HEX HD M6 X 12 LOCK
20229		1	SEAL RING UPPER
21038		7	WASHER FLAT 6.90X20.50X1.88
24401		1	HOUSING MACHINED FRONT
24409		3	PISTON SLAVE 22.2 MM DIA
24423		3	SLEEVE HOUSING ADJUSTING
24435		3	D-LASH .153 STROKE
24614		1	SOLENOID 12VDC S/L V-BLADE
25840		1	PLATE ID 490 FRONT 12VDC
25842		3	PISTON MASTER 15.856 MM DIA

ISL 490 Parts Info
REAR HOUSING

Customer Part Number Cross Reference

Customer	Part Number
CUMMINS	3948275

Where Used Listing

Part	*	Qty	Desc
26309		1	<obs>HSG ASSY REAR 12VDC PKGD
1024405		1	HSG ASSY REAR 12VDC PKGD 490
5024405		1	HOUSING ASSY REAR 12VDC BULK

Bill of Materials Listing

Part	*	Qty	Desc
1082		1	SEAL RING - CENTER
1083		1	SEAL RING - LOWER
7500		3	SPRING C/V INNER ORANGE
9922		2	DRIVE SCREW #4 X 1/4 LG
11251		3	COLLAR CONTROL VALVE
11259		1	SPRING CHECK VALVE STOP
11260		1	RETAINER SPRING CHECK VALVE
11261		1	RING RETAINER CHECK VALVE
11262		1	BALL 9/32 DIA GRADE 25
11283		3	SPOOL ASSY CONTROL VALVE
11284		3	RING RETAINER CONTROL VALVE
11395		3	NUT HEX JAM 1/2-20
11434		3	SPRING C/V OUTER WHITE
12983		1	PISTON ACCUMULATOR
12990		1	SPRING
12991		4	RING RETAINING
13500		3	RETAINER SPRING SLAVE PISTON
18209		3	SPRING INNER SLAVE PISTON
18485		12	PLUG PIPE FLUSH SEAL 1/16-27
18722		3	SPRING FLAT
18730		3	SCR HEX HD M6 X 12 LOCK
20229		1	SEAL RING UPPER
21038		7	WASHER FLAT 6.90X20.50X1.88
24404		1	HOUSING MACHINED REAR
24409		3	PISTON SLAVE 22.2 MM DIA
24423		3	SLEEVE HOUSING ADJUSTING
24435		3	D-LASH .153 STROKE
24614		1	SOLENOID 12VDC S/L V-BLADE
25841		1	PLATE ID 490 REAR 12VDC
25842		3	PISTON MASTER 15.856 MM DIA