

QSK50-G2

Emissions Compliance:
EPA NSPS Stationary Emergency Tier 2



> Specification sheet



Our energy working for you.™

Description

The QSK50 is a V 16 cylinder engine with a 50 litre displacement. This Quantum series utilizes sophisticated electronics and premium engineering to provide outstanding performance levels, reliability and versatility for Standby, Prime and Continuous Power applications.



This engine has been built to comply with CE certification.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

Features

High pressure fuel pump, Modular Common Rail fuel System (MCRS) and state of the art integrated electronic control system provide superior performance, efficiency and diagnostics. The electronic fuel pumps deliver up to 1600 bar injection pressure and eliminate mechanical linkage adjustments. The new MCRS utilizes an electric priming pump which is integrated with the off-engine stage-1 fuel filter head and is controlled and powered by the engine ECM. The stage-2 fuel filters are mounted on-engine

CTT (Cummins Turbo Technologies) HX82/HX83 turbo-charging utilizes exhaust energy with greater efficiency for improved emissions and fuel consumption.

Low Temperature After-cooling - Two-pump Two-loop (2P2L)

Ferrous Cast Ductile Iron (FCD) Pistons - High strength design delivers superior durability.

G-Drive Integrated Design - Each component has been specifically developed and rigorously tested for G-Drive products, ensuring high performance, durability and reliability.

Service and Support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class service network.

1500 rpm (50 Hz Ratings)

Gross Engine Output			Net Engine Output			Typical Generator Set Output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP			kWm/BHP			kWe	kVA	kWe	kVA	kWe	kVA
1260/1690	1108/1486	997/1337	1213/1627	1074/1440	963/1291	1120	1400	1020	1275	924	1155

1800 rpm (60 Hz Ratings)

Gross Engine Output			Net Engine Output			Typical Generator Set Output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP			kWm/BHP			kWe	kVA	kWe	kVA	kWe	kVA

Our energy working for you.™

www.cumminsgdrive.com

©2011 | Cummins G-Drive Engines | Specifications Subject to Change Without Notice | Cummins is a registered trademark of Cummins Inc. (10/11) (GDSS159)



1396/1872	1210/1623	1089/1460	1344/1802	1172/1572	1051/1409	1250	1563	1135	1419	1008	1261
-----------	-----------	-----------	-----------	-----------	-----------	------	------	------	------	------	------

Our energy working for you.™

www.cumminsgdrive.com

©2011 | Cummins G-Drive Engines | Specifications Subject to Change Without Notice | Cummins is a registered trademark of Cummins Inc.
(10/11) (GDSS159)



General Engine Data

Type	4 cycle, Turbocharged, After-cooled		
Bore mm	159		
Stroke mm	159		
Displacement Litre	50.3		
Cylinder Block	Cast iron, 16 cylinder		
Battery Charging Alternator	55A		
Starting Voltage	24V		
Fuel System	Direct injection Cummins MCRS		
Fuel Filter	Spin on fuel filters with water separator		
Lube Oil Filter Type(s)	Spin on full flow filter		
Lube Oil Capacity (l)	235		
Flywheel Dimensions	SAE 0		

Coolpac Performance Data

Cooling System Design	2 pump - 2 loop		
Coolant Ratio	50% ethylene glycol; 50% water		
Coolant Capacity (l)	294		
Limiting Ambient Temp (°C)**	53 (50Hz)	51 (60Hz)	
Fan Power (kWm)	40 (50Hz)	50 (60Hz)	
Cooling System Air Flow (m ³ /s)**	35 (50Hz)	35 (60Hz)	
Air Cleaner Type	Dry replaceable element with restriction indicator		

** @ 13 mm H₂O

Ratings Definitions

Emergency Standby Power (ESP):

Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Limited-Time Running Power (LTP):

Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.

Prime Power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Base Load (Continuous) Power (COP):

Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

Weight & Dimensions

Length	Width	Height	Weight (dry)
mm	mm	mm	kg
4674	2468	3100	7429

Fuel Consumption 1500 rpm (50 Hz)

%	kWm	BHP	L/ph	US gal/ph
Standby Power				
100	1260	1689	323	85.1
Prime Power				
100	1108	1485	286	75.5
75	831	1114	226	59.6
50	554	743	157	41.3
25	227	371	84	22.1
Continuous Power				
100	997	1337	258	68.2

Fuel Consumption 1800 rpm (60 Hz)

%	kWm	BHP	L/ph	US gal/ph
Standby Power				
100	1396	1872	350	92.5
Prime Power				
100	1210	1622	306	80.8
75	908	1217	242	63.9
50	605	811	168	44.3
25	303	406	100	26.5
Continuous Power				
100	1089	1460	282	74.3

Cummins G-Drive Engines

Asia Pacific

10 Toh Guan Road
#07-01
TT International Tradepark
Singapore 608838
Phone 65 6417 2388
Fax 65 6417 2399

Europe, CIS, Middle East and Africa

Manston Park Columbus Ave
Manston Ramsgate
Kent CT12 5BF. UK
Phone 44 1843 255000
Fax 44 1843 255902

Latin America

Rua Jati, 310, Cumbica
Guarulhos, SP 07180-900
Brazil
Phone 55 11 2186 4552
Fax 55 11 2186 4729

Mexico

Cummins S. de R.L. de C.V.
Eje 122 No. 200 Zona Industrial
San Luis Potosi, S.L.P. 78090
Mexico
Phone 52 444 870 6700
Fax 52 444 870 6811

North America

1400 73rd Avenue N.E.
Minneapolis, MN 55432
USA
Phone 1 763 574 5000
USA Toll-free 1 877 769 7669
Fax 1 763 574 5298

Our energy working for you.™

www.cumminsgdrive.com

©2011 | Cummins G-Drive Engines | Specifications Subject to Change Without Notice | Cummins is a registered trademark of Cummins Inc. (10/11) (GDSS159)

