QSK60-G7



> Specification sheet



Our energy working for you.™

Description

The QSK60 is a V 16 cylinder engine with a 60 litre displacement. This Quantum series utilizes sophisticated electronics and premium engineering to provide outstanding performance levels, reliability and versatility for Standby, Prime and Continuous Power applications



This engine has been built to comply with CE certification.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

Features

High pressure fuel pump, Modular Common Rail fuel System (MCRS) and state of the art integrated electronic control system provide superior performance, efficiency and diagnostics. The electronic fuel pumps deliver up to 1600 bar injection pressure and eliminate mechanical linkage adjustments. The new MCRS utilizes an electric priming pump which is integrated with the off-engine stage-1 fuel filter head and is controlled and powered by the engine ECM. The stage-2 fuel filters are mounted on-engine

CTT (Cummins Turbo Technologies) HX82/HX83 turbocharging utilizes exhaust energy with greater efficiency for improved emissions and fuel consumption.

Low Temperature After-cooling - Two-pump Two-loop (2P2L)

Ferrous Cast Ductile Iron (FCD) Pistons - High strength design delivers superior durability.

G-Drive Integrated Design - Each component has been specifically developed and rigorously tested for G-Drive products, ensuring high performance, durability and reliability.

Service and Support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class service network.

1500 rpm (50 Hz Ratings)

Gross Engine Output			Net	Engine Out	put	Typical Generator Set Output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
	kWm/BHP			kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA
1790/2399	1615/2165	1305/1749	1737/2329	1580/2119	1270/1703	1825	2000	1517	1825	1219	1524

1800 rpm (60 Hz Ratings)

Gross Engine Output			Net	Engine Out	put	Typical Generator Set Output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP				kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA
2180/2922	1975/2647	1740/2332	2120/2843	1937/2598	1702/2282	2000	2500	1825	2281	1633	2042

Our energy working for you.™



General Engine Data

Туре	4 cycle, Turbocharged, After-cooled			
Bore mm	159			
Stroke mm	190			
Displacement Litre	60.2			
Cylinder Block	Cast iron, 16 cylinder			
Battery Charging Alternator	55A			
Starting Voltage	24V			
Fuel System	Direct injection Cummins MCRS			
Fuel Filter	Spin on fuel filters with water separator			
Lube Oil Filter Type(s)	Spin on full flow filter			
Lube Oil Capacity (I)	280			
Flywheel Dimensions	SAE 0			

Coolpac Performance Data

Cooling System Design	2 pump - 2 loop			
Coolant Ratio	50% ethylene glycol; 50% water			
Coolant Capacity (I)				
Limiting Ambient Temp.**	Engine only – not applicable			
Fan Power	Engine only – not applicable			
Cooling System Air Flow (m ³ /s)**				
Air Cleaner Type	Dry replaceable element with restriction indicator			

** @ 13 mm H²0

Ratings Definitions

Emergency Standby Power (ESP):

Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Limited-Time Running Power (LTP):

Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.

Prime Power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Base Load (Continuous) Power (COP):

Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

Weight & Dimensions

Length	Width	Height	Weight (dry)	
mm	mm	mm	kg	
2781	1794	2155	7185	

Fuel Consumption 1500 (50 Hz)

%	kWm	BHP	L/ph	US gal/ph				
Standby Power								
100	1790	2399	415	109.5				
Prime Power								
100	1615	2165	378	99.7				
75	1211	1624	288	75.9				
50	808	1083	200	52.9				
25	404	541	115	30.3				
Continuous Power								
100	1305	1749	309	81.6				

Fuel Consumption 1800 (60 Hz)

%	kWm	BHP	L/ph	US gal/ph					
Standby Power									
100	2180	2922	520	137.2					
Prime Power									
100	1978	2647	471	124.2					
75	1481	1985	360	95.1					
50	987	1324	254	67.1					
25	494	662	152	40.1					
Continuous Power									
100	1740	2332	417	110					

Cummins G-Drive Engines

Asia Pacific 10 Toh Guan Road #07-01 TT International Tradepark Singapore 608838 Phone 65 6417 2388 Fax 65 6417 2399 Europe, CIS, Middle East and Africa Manston Park Columbus Ave Manston Ramsgate Kent CT12 5BF. UK Phone 44 1843 255000 Fax 44 1843 255902 Latin America Rua Jati, 310, Cumbica Guarulhos, SP 07180-900 Brazil Phone 55 11 2186 4552 Fax 55 11 2186 4729 Mexico Cummins S. de R.L. de C.V. Eje 122 No. 200 Zona Industrial San Luis Potosí, S.L.P. 78090 Mexico Phone 52 444 870 6700 Fax 52 444 870 6811 North America 1400 73rd Avenue N.E. Minneapolis, MN 55432 USA Phone 1 763 574 5000 USA Toll-free 1 877 769 7669 Fax 1 763 574 5298

Our energy working for you.™

