

6LTAA9.5-G1



Description

The Cummins® 6LTAA9.5-G engine has a mechanical fuel system which is designed to deliver robust performance in the most extreme conditions. It also has electronic governor controls for superior engine speed stability and transient response. The cylinder head has 24-valves and bigger flow injector design which provides one of the highest power-toweight ratios in its class.

At the same time, the 6LTAA9.5-G engine delivers better fuel economy and less smoke emission than similar engines.

Features

Fuel system - Bosch P7100 type mechanical fuel injection pumps have high injection pressure, optimize engine performance and establish an unrivalled reputation for reliability.

Electronic governor control unit - Strengthening electronic governor control unit to optimize engine speed stability, transient response and reliability.

Cummins Holset HE400 and HE500 Nonwastegate turbocharger - Cummins optimized turbocharger delivers increased power, fuel economy, low smoke and lower noise levels.

Electronic fuel shut off valve - Robust design for safety for mechanical fuel system engine.

Integrated block design - Integrated fluid circuits replace hoses and eliminate potential leaks.

24-valve cylinder head - Four valves per cylinder for increased power with faster response and improved fuel economy.

Coolpac integrated design - Products are supplied complete with cooling package and air cleaner kit for a complete power package. Each component has been specifically developed and rigorously tested for Cummins G-Drive standards, ensuring high performance, durability and reliability.

Service and support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class global service network.



This engine has been built to comply with CE certification.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

1500 rpm (50 Hz ratings)

Gross engine output			Net engine output		Typical generator set output						
Standby Prime Base		Standby	Prime	Base	Standby (ESP)		by (ESP) Prime		Base (COP)		
	kWm/BHP		kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA	
320/429	290/389	254/340	300/402	273/366	237/318	280	350	256	320	220	276

1800 rpm (60 Hz ratings)

Gross engine output			Net engine output		Typical generator set output						
Standby Prime Base		Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)		
	kWm/BHP		kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA	
310/416	280/375	244/327	292/392	265/355	229/307	275	344	250	313	212	265

General engine data

Туре	4 cycle, in-line, turbocharged, air-cooled
Bore mm	116 mm (4.58 in.)
Stroke mm	148 mm (5.82 in.)
Displacement litre	9.5 litre (579 in. ³)
Cylinder block	Cast iron, 6 cylinder
Battery charging alternator	70 amps
Starting voltage	24 volt, negative ground
Fuel system	Bosch direct injection
Fuel filter	Spin-on fuel filters with water separator
Lube oil filter type(s)	Spin-on full flow filter
Lube oil capacity (I)	28.1
Flywheel dimensions	SAE1

Coolpac performance data

Cooling system design	Air-air charge cooled			
Coolant ratio	50% ethylene glycol; 50% water			
Coolant capacity (I)	55.5			
Limiting ambient temp.** (°C)	50 (50 Hz); 55 (60 Hz)			
Fan power (kWm)	13 (50 Hz); 15 (60 Hz)			
Cooling system air flow (m³/s)**	7.9 (50 Hz); 10 (60 Hz)			
Air cleaner type	Light duty dry replaceable element with restriction indicator			


^{** @ 13} mm H₂0

Fuel consumption 1500 (50 Hz)

%	kWm	ВНР	L/ph	g/kWh					
Standby P	Standby Power								
100	320	429	78	200					
Prime Pow	Prime Power								
100	290	389	70	199					
75	218	291	52	196					
50	145	194	35	197					
25	73	97	18	210					
Continuous Power									
100	254	340	61	198					

Fuel consumption 1800 (60 Hz)

%	kWm	ВНР	L/ph	g/kWh				
Standby P	Standby Power							
100	310	415	76	201				
Prime Pow	Prime Power							
100	280	375	68	199				
75	210	281	50	197				
50	140	188	34	200				
25	70	94	19	221				
Continuous Power								
100	244	327	56	198				



Weights and dimensions

Length	Width	Height	Weight (dry)
mm	mm	mm	kg
2110	1102	1489	945

Ratings definitions

Emergency Standby Power (ESP):	Limited-Time Running Power (LTP):	Prime Power (PRP):	Base Load (Continuous) Power (COP):
Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.	Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

For more information contact your local Cummins distributor or visit power.cummins.com

