QST30-G5

Emissions Compliance: EPA NSPS Stationary Emergency Tier 2



> Specification sheet



Our energy working for you.™

Description

The QST30 Quantum series utilises sophisticated electronics and premium engineering to provide outstanding performance levels from its compact 30 litre, V12 configuration. In fact, the QST30-Series delivers more power and torque in a smaller package than any other diesel engine on the market.



This engine has been built to comply with CE certification.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

Features

Quantum electronic fuel systems and controls provide superior performance, efficiency and diagnostics. The electronic fuel pumps deliver up to 1100 bar injection pressure and eliminate mechanical linkage adjustments.

CTT (Cummins Turbo Technologies) HX82 turbocharging utilises exhaust energy with greater efficiency for improved emissions and fuel consumption.

Charge Air Cooling – Utilizing an Air-to-Air heat exchanger or Charge-Air-Cooler (CAC) to reduce intake manifold temperature and to meet the lower emissions requirements.

Cast Iron Pistons – High strength design delivers superior durability.

Coolpac Integrated Design - Products are supplied complete with cooling package and air cleaner kit for a complete power package. Each component has been specifically developed and rigorously tested for G-Drive products, ensuring high performance, durability and reliability.

Service and Support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class service network.

1800 rpm (60 Hz Ratings)

Gross Engine Output			Net Engine Output			Typical Generator Set Output					
Standby	Prime	Base	Standby	Prime	Base	Standby (ESP)		Prime (PRP)		Base (COP)	
kWm/BHP			kWm/BHP			kWe	kVA	kWe	kVA	kWe	kVA
1112/1490	1007/1350	832/1115	1069/1434	975/1308	800/1073	1000	1250	910	1138	752	940

Our energy working for you.™



General Engine Data

Type 4 cycle, Turbocharged and After cooled

 Bore mm
 140

 Stroke mm
 165

 Displacement Litre
 30.5

Cylinder Block Cast iron, 50°V 12 cylinder

Battery Charging Alternator 35A Starting Voltage 24V

Fuel System Direct injection

Fuel Filter Spin on fuel filters with water separator

Lube Oil Filter Type(s) Spin on full flow filter

Lube Oil Capacity (I) 40.7 Flywheel Dimensions SAE 0

Coolpac Performance Data

Cooling System Design Air-air charge cooled

Coolant Ratio 50% ethylene glycol; 50% water

Coolant Capacity (I) 202
Limiting Ambient Temp. (°C)** 50.0
Fan Power (kWm) 42.4
Cooling System Air Flow (m³/s)** 16.0

Air Cleaner Type Dry replaceable element with restriction indicator
** @ 13 mm H²0

Ratings Definitions

Emergency Standby Power (ESP):

Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789,

DIN 6271 and BS 5514.

Limited-Time Running Power (LTP):

Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with

ISO 8528.

Prime Power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Base Load (Continuous) Power (COP):

Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

Weight & Dimensions

Length	Width	Height	Weight (dry)	
mm	mm	mm	kg	
2772	1752	2226	3822	

Fuel Consumption 1800 rpm (60 Hz)

%	% kWm		L/ph	US gal/ph			
Standby Power							
100	1112	1490	275	72.7			
Prime Power							
100	1007	1350	248	65.4			
75	755	1013	185	48.8			
50	504	675	126	33.1			
25	252	338	69	18.2			
Continuous Power							
100	832	1115	246	64.9			

Cummins G-Drive Engines

Asia Pacific 10 Toh Guan Road #07-01

TT International Tradepark Singapore 608838 Phone 65 6417 2388 Fax 65 6417 2399 Europe, CIS, Middle East and Africa Manston Park Columbus Ave Manston Ramsgate Kent CT12 5BF. UK Phone 44 1843 255000

Fax 44 1843 255902

Latin America Rua Jati, 310, Cumbica Guarulhos, SP 07180-900 Brazil Phone 55 11 2186 4552 Fax 55 11 2186 4729 Mexico Cummins S. de R.L. de C.V. Eje 122 No. 200 Zona Industrial San Luis Potosí, S.L.P. 78090 Mexico Phone 52 444 870 6700 Fax 52 444 870 6811 North America 1400 73rd Avenue N.E. Minneapolis, MN 55432 USA Phone 1 763 574 5000 USA Toll-free 1 877 769 7669 Fax 1 763 574 5298





