Specification sheet



QSG12-G1



Description

The QSG12 engine is designed with fewer parts and less weight to provide higher reliability and more convenient maintenance. Featuring the Cummins High Pressure Common Rail (HPCR) fuel system, the QSG12 has evolved from the proven and successful base platform of an automotive engine, which is widely accepted for its high levels of in-service reliability and performance.

The QSG12 engine also has excellent derating performance for temperature and altitude; when coupled with 50°C ambient capable cooling system, it makes these engines the best performers in the harshest conditions.

Features

Cummins High Pressure Common Rail (HPCR) Fuel System – Most capable common-rail fuel system utilized on a heavy-duty engine, enabling faster and smoother power delivery with lower fuel consumption.

Coolpac Integrated Design - Products are supplied complete with cooling package and normal-duty air cleaner kit for a complete power package. A heavyduty air cleaner is offered as an option.

Full Authority Electronic Engine - Advanced engine monitoring, diagnostics, protection and control, coupled with the HPCR fuel system, capable of delivering extreme fuel injection pressures with multiple injection events, improved fuel efficiency, lower noise and enhanced engine performance.

Controls - Fitted with the Cummins CM2880 ECM that utilizes the latest in microprocessor technology. Includes the Cummins proprietary Power Generation Interface (PGI); the widely accepted SAE J1939 industry standard CAN based communication network provides advanced engine protection, ensuring faster connectivity along with a superior fault-finding capability.

Fuel Filtration System – Fleetguard two-stage fuel filtration system using NanoNetTM nanomedia can effectively block impurities as small as 5 microns and includes water in fuel (WIF) sensor. This provides reliable protection for engine fuel system components against fuel contaminated with dust, dirt or water.

Lube Filtration System – Fleetguard Lube Filter using patented StrataPoreTM filter paper delivers best in class performance while providing high efficiency filtration for extended protection to the engine and components.

Reduced Operating Costs – 500 hours for standard oil and filter changes.

Service and support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class service network.



This engine has been built to comply with CE certification.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002.

1500 rpm (50 Hz ratings)

Gross engine output			Net engine output		Typical generator set output						
Standby	Prime	Base	Standby	Prime	Base	Standb	y (ESP)	Prime	(PRP)	Base	(COP)
	kWm/BHP			kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA
369/495	332/445	291/401	349/468	312/419	279/374	320	400	288	360	260	325

General engine data

Туре	6 cycle, in-line, turbocharged, air-cooled		
Bore mm	132 mm (5.20 in.)		
Stroke mm	144 mm (5.67 in.)		
Displacement litre	11.8 litre (721 in. ³)		
Cylinder block	Cast iron, 6 cylinder		
Battery charging alternator	80 amps		
Starting voltage	24 volt, negative ground		
Fuel system	HPCR		
Fuel filter	Spin-on fuel filters with water separator		
Lube oil filter type(s)	Spin-on full flow filter		
Lube oil capacity (I)	34.1		
Flywheel dimensions	SAE1		


Coolpac performance data

Coolant ratio 50% ethylene glycol; 50% water Coolant capacity (I) 48.0 Limiting ambient temp.** (°C) 50	system design	Air-air charge cooled		
	ratio 5	50% ethylene glycol; 50% water		
Limiting ambient temp.** (°C) 50	capacity (I)	48.0		
	ambient temp.** (°C)	50		
Fan power (kWm) 14.08	ver (kWm)	14.08		
Cooling system air flow (m³/s)** 7.15	system air flow (m³/s)**	7.15		
Air cleaner type Normal duty dry replaceable element with restriction indicator	ner type	Normal duty dry replaceable element with restriction indicator		

^{** @ 13} mm H₂0

Fuel consumption 1500 (50 Hz)

%	kWm	ВНР	L/ph	g/kWh			
Standby Power							
100	369	495	82	188			
Prime Power							
100	332	445	72	184			
75	249	334	54	184			
50	166	223	37	188			
25	83	111	20	203			
Continuous Power							
100	299	401	64	183			



Weights and dimensions

Length	Width	Height	Weight (dry)
mm	mm	mm	kg
2293	1083	1705	1010

Ratings definitions

Emergency Standby Power (ESP):	Limited-Time Running Power (LTP):	Prime Power (PRP):	Base Load (Continuous) Power (COP):
Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.	Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

For more information contact your local Cummins distributor or visit power.cummins.com

