Specification sheet



KTA38-G4 Fuel Optimized



Description

The KTA38-Series benefits from years of technical development and improvement to bring customers an innovative and future proof diesel engine that keeps pace with ever changing generator set requirements.

Recognized globally for its performance under even the most severe climatic conditions, the KTA38-Series is widely acknowledged as the most robust and cost-effective diesel engine in its power range for the generator set market.

Features

Aftercooler – Large capacity after cooler results in cooler, denser intake air for more efficient combustion and reduced internal stresses for longer life.

Fuel System – Cummins exclusive lowpressure PT[™] system with wear compensating pump and integral dual flyweight governor. Camshaft actuated fuel injectors give accurate metering and timing. Fuel lines are internal drilled passages in cylinder heads. Spin-on fuel filter.

Cooling System – Gear driven centrifugal water pump. Large volume water passages provide even flow of coolant around cylinder liners, valves and injectors. Bypass thermostats regulate coolant temperature. Spin-on corrosion resistors check rust and corrosion, control acidity and remove Impurities.



This engine has been designed in facilities certified to ISO9001 and manufactured in facilities certified to ISO9001 or ISO9002. **Cylinder Block** – Alloy cast iron with removable wet liners. Cross bolt support to main bearing cap provides extra strength and stability.

Service and Support - G-Drive products are backed by an uncompromising level of technical support and after sales service, delivered through a world class service network.

Turbocharger – Cummins Turbo Technologies (CTT) exhaust gas driven turbocharger mounted at top of engine provides more power, improved fuel economy, altitude compensation, and lower smoke and noise levels.

1500 rpm (50 Hz ratings)

Gross engine output		Net engine output		Typical generator set output							
Standby	Prime	Base	Standby	Prime	Base	Standb	y (ESP)	Prime	(PRP)	Base	(COP)
	kWm/BHP		kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA	
-	-	-	-	-	-	-	-	-	-	-	-

1800 rpm (60 Hz ratings)

Gross engine output		Net engine output		Typical generator set output							
Standby Prime Base		Standby	Prime	Base	Standby (ESP)		P) Prime (PRP)		Base (COP)		
	kWm/BHP		kWm/BHP		kWe	kVA	kWe	kVA	kWe	kVA	
1112/1490	1007/1350	776/1040	1063/1425	969/1299	738/989	1000	1250	910	1138	700	875

General engine data

Туре	4 cycle, 60 degree Vee, turbocharged, aftercooled		
Bore mm	159 mm (6.25 in.)		
Stroke mm	159 mm (6.25 in.)		
Displacement litre	37.8 litre (2300 in. ³)		
Cylinder block	Cast iron, 12 cylinder		
Battery charging alternator	35 amps		
Starting voltage	24 volt, negative ground		
Fuel system	Direct injection, EFC (Electronic Fuel Control) governor		
Fuel filter	Dual spin-on paper element fuel filters with water separator		
Lube oil filter type(s)	Spin-on full flow filter		
Lube oil capacity (I)	140		
Flywheel dimensions	SAE 0		

Coolpac performance data

Cooling system design	JWAC
Coolant ratio	50% ethylene glycol; 50% water
Coolant capacity (I)	218.5
Limiting ambient temp.** (°C)	50
Fan power (kWm)	35
Cooling system air flow (m ³ /s)**	24.6
Air cleaner type	Dry replaceable element with restriction indicator


** @ 13 mm H₂0

Fuel consumption 1500 (50 Hz)

%	kWm	BHP	L/ph	g/kWh			
Standby Power							
100	-	-	-	-			
Prime Pow	Prime Power						
100	-	-	-	-			
75	-	-	-	-			
50	-	-	-	-			
25	-	-	-	-			
Continuous Power							
100	-	-	-	-			

Fuel consumption 1800 (60 Hz)

%	kWm	BHP	L/ph	g/kWh			
Standby Power							
100	1112	1490	271	71.5			
Prime Power							
100	1007	1350	245	64.6			
75	755	1012	190	50.1			
50	504	675	136	36.0			
25	252	338	81	21.5			
Continuous Power							
100	776	1040	193	51.0			



Weights and dimensions

Length	Width	Height	Weight (dry)
mm	mm	mm	kg
3172	1752	2004	4990

Ratings definitions

Emergency Standby	Limited-Time Running	Prime Power (PRP):	Base Load (Continuous)
Power (ESP):	Power (LTP):		Power (COP):
Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power to a constant electrical load for limited hours. Limited-Time Running Power (LTP) is in accordance with ISO 8528.	Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.	Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN6271 and BS 5514.

For more information contact your local Cummins distributor or visit cummins.com



Our energy working for you.™

©2019 Cummins Inc. All rights reserved. Cummins is a registered trademark of Cummins Inc. PowerCommand, AmpSentry, InPower and "Our energy working for you." are trademarks of Cummins Inc. Other company, product, or service names may be trademarks or service marks of others. Specifications are subject to change without notice. KTA38-G4 (4/19)