

# Diesel Generator Set QSK60 Series

2250-2500 kVA Standby



# **Reliable and Durable**

Cummins<sup>®</sup> 'QSK60 series' (Quantum leap in product technology) diesel engine with strong regrindable crankshaft, high strength connecting rod, high pressure injection full authority electronic fuel system, 2 pump 2 loop coolant system. 'QSK60 series' generating sets are more reliable and durable. Engines have clocked millions of hours operating in some of the world's most demanding conditions. Current engines are regularly upgraded with new technologies for better performance and economy. The ultimate proof of superior performance and reliability is the fact that Cummins<sup>®</sup> manufactures these engines in India.

# **Unmatched Warranty**

Cummins<sup>®</sup> 'QSK60 series' diesel engine generating sets are a truly cost effective solution to long term power need backed by industry best, 2 years / 5000 hrs warranty, for the entire generating set. With superior experience in technology , design capability, commitment, reliability and quality we offer an unmatched 5 years or 5000 hours (including above 2 years) warranty coverage on 5 critical components (5C) of the engine – Cylinder Head, Camshaft, Crankshaft, Cylinder Block, Connecting Rod against manufacturing defect ( 5C warranty is offered only for India source product.

## **Cummins Advantage**

Special features of Cummins<sup>®</sup> 'QSK60 series' engines like full authority electronic injection, low temperature aftercooler, optimised turbocharging and precision injection timing make these engines the ultimate in exceptional fuel efficiency all across the operating range.

## **Single Source Power Assurance**

Design, manufacture and testing of engine, alternator and other accessories is done by Cummins Group of companies for optimum performance and is backed by a countrywide product the entire package.



# Standard scope

**Engine:** Cummins<sup>®</sup> 'QSK60 series' full authority electronic injection, water cooled engine, 16 cylinder, 4 stroke, rated at 1500 RPM, conforming to ISO 3046 /IS 13018 has the following specifications:

- Cummins Full Authority electronics
- Cummins HPI injectors
- Cummins turbocharger, pulse tuned exhaust manifold, stainless steel exhaust flexible connections (4 Turbos)
- Radiator or heat exchanger, coolant inhibitor
- Plate type lube oil cooler
- Outboard aftercoolers
- Full flow paper element filters fuel, lube oil and bypass
- Dry type replaceable paper element air cleaner with restriction indicator
- Flywheel housing & flywheel to suit single bearing alternator
- Starting motor Electric
- Battery charging alternator
- Cummins PowerCommand<sup>®</sup> microprocessor based genset controller
- First fill lube oil
- Alternator: Stamford brushless alternator

Seperately excited, self-regulated

- Salient pole revolving field
- Single / double bearing
- VPI epoxy impregnated insulation technology
- Re-greasable deep groove Single bearing
- The-greasable deep groove on great
  Evolution
  DMC based brueblase
- Excitation PMG based brushless
- Space heaters, RTD/BTD (without scanner).

## Accessories:

- Silencer suitably optimized to reduce noise
- Sturdy base rail
- 990 ltrs. free standing fuel tank
- Batteries with connecting leads and terminals

#### QSK60 2250-2500 kVA Standby

#### **Optionals**

**Engine:** Lube oil / Coolant heater with thermostatic switch, Air Starter

#### Alternator: Double Bearing

**Control Panel:** AMF control panel, Battery charger, Remote/ Auto start panel, Auto/Manual synchronizing panel, Audio/ Visual annunciation for faults

**Oil Pan:** 398 lts. oil pan for extended oil change interval for 2250 kVA

# Control panel: PowerCommand<sup>®</sup> PC 3.3 with MLD



The PowerCommand<sup>®</sup> control

system is an integrated microprocessor based generator set control system providing voltage regulation, engine protection, alternator protection, operator interface and isochronous governing.

**AmpSentry™** – Includes integral AmpSentry™ protection, which provides a full range of alternator protection function which are matched to the alternator provided.

**Power Management** – Control function provides battery monitoring, testing and a smart starting control system.

**Advanced Control Methodology** – Three phase sensing, FET based full wave rectified voltage regulation and a PWM output for stable operation with all load types.

**Communications Interface** – Control comes standard with PCCNet and Modbus interface.

**Regulation Compliant** – Prototype tested: UL, CSA and CE compliant.

**Service** - InPower™ PC-based service tool available for detailed diagnostics, setup, data logging and fault simulation.

**Reliable Design** – For reliable operations in harsh environment.

#### Multi-language support

Independent of PC/ laptop for setting up

# **Operator panel features**

**Operator Panel Features** – The operator panel, in addition to the alternator, displays the Utility/ AC Bus data.

## **Operator/ Display Functions**

- 320 x 240 pixels graphic LED backlight LCD with bar graph for displaying electrical parameters
- Auto, manual, start, stop, fault reset and lamp test/panel lamp switches
- Alpha-numeric display with pushbuttons
- LED lamps indicating genset running, remote start, not in auto, common shutdown, common warning, manual run mode, auto mode and stop

#### **Paralleling Control Functions**

- Digital frequency synchronization and voltage matching
- Isochronous kW and kvar load sharing controls
- Droop kW and kvar control
- Sync check
- Extended paralleling (Peak Shave/Base Load)
- Digital power transfer control (AMF) provides load transfer operation in open or closed transition or soft (ramping) transfer mode

#### **Alternator Data**

- Line-to-neutral and line-to-line AC volts
- 3-phase AC current
- Frequency
- kW, kvar, power factor kVA (three phase and total)

#### **Engine Data**

- DC voltage
- Engine speed
- Lube oil pressure
- Coolant temperature/ low level
- Comprehensive FAE data (where applicable)

# **Other Data**

- Genset model data
- Start attempts, starts, running hours, kW hours
- Load profile (operating hours at % load in 5% increments)
- Fault history
- Data logging and fault simulation (requires InPower)
- Standard control functions

#### Digital Governing

- Integrated digital electronic isochronous governor
- Temperature dynamic governing

#### **Digital Voltage Regulation**

- Integrated digital electronic voltage regulator
- 3-phase, 4-wire line-to-line sensing
- Configurable torque matching

#### AmpSentry<sup>™</sup> AC Protection

- AmpSentry<sup>™</sup> protective relay
  - Over current and short circuit shutdown
  - Over current warning
  - Single and three phase fault regulation
  - Over and under voltage shutdown
  - Over and under frequency shutdown
  - Overload warning with alarm contact
  - Reverse power and reverse var shutdown

# Field overload

- Engine protection
- Battery voltage monitoring, protection and testing
- Over speed shutdown
- Low oil pressure warning and shutdown
- High coolant temperature warning and shutdown
- Low coolant level warning or shutdown
- Low coolant temperature warning
- Fail to start (over crank) shutdown
- Fail to crank shutdown
- Cranking lockout
- Sensor failure indication
- Low fuel level warning or shutdown

#### **MLD** features

- Load dependent start/stop
- Run hour equalization
- Built-in Logic
- Single point MLD setting
- System monitoring
- Master-less
- Single point remote start
- Predictive Load input
- Dedicated screens

# **Technical Data**

Generator set specifications					
Model	C2250 D5S		C2500 D5S		
Standby Power Rating kVA	2250		2500		
Output Voltage and Frequency	415V/ *3.3/ *6.6/ 11KV - 50Hz		415V/ *3.3/ *6.6/ 11KV - 50Hz		
Power Factor	0.8 (lag)		0.8 (lag)		
No. of phases	3 phase		3 phase		
	- 1				
Engine specifications	1		I		
Make	Cummins		Cummins		
Model	QSK 60 G4		QSK 60 G8		
No. of cylinders	16		16		
Aspiration	Turbocharged - LTA Aftercooled		Turbocharged - LTA Aftercooled		
Bore x Stroke	159 mm x 190 mm		159 mm x 190 mm		
Displacement	60.2 ltrs		60.2 ltrs		
Output - Standby	2567 bhp (1950 kWm)		2875 bhp (2145 kWm)		
Fuel consumption @ 75% load with Rad/HE	327/316 ltr/hr		368/358 ltr/hr		
Fuel consumption @ 100% load with Rad/HE 390/380 ltr/hr	436/426 ltr/hr		496/485 ltr/hr		
Total wet weight ( engine + radiator)	9904 kg		9904 kg		
Length x Width x Height (engine)	2780 x 1591 x 1960 mm		2780 x 1591 x 1960 mm		
Compression Ratio	14.5:1		14.5:1		
Piston Speed	9.5 m/s		9.5 m/s		
Governor / Class	Electronic / A1		Electronic / A1		
Lubricating oil sytem capacity	280/398 ltrs		398 ltrs		
Coolant capacity (engine + radiator)	621 ltrs		621 ltrs		
Combustion air intake @ 100% load (+/- 5%)	144 m <sup>3</sup> /min		156 m <sup>3</sup> /min		
Exhaust Temperature	460 °C		485 °C		
Alternator specifications					
Make	Stamford-LT	Stamford-HT	Stamford-LT	Stamford-HT	
Frame size / Model No.	PI734H	HVSI804R	P1734H	HVSI804R	
Voltage Regulation	± 0.5%	± 0.5%	± 0.5%	± 0.5%	
Insulation	Class H	Class F	Class H	Class F	
Standard Enclosure	IP 23	IP 23	IP 23	IP 23	
Winding Pitch	2/3 Pitch	2/3 Pitch	2/3 Pitch	2/3 Pitch	
Stator Winding	Double layer lap,form wound	Double layer lap, form wound	Double layer lap, form wound	Double layerlap, form wound	
Rotor Dynamically balanced with grade 2.5	Dynamically balanced with grade 2.5	Dynamically balanced with grade 2.5	Dynamically balanced with grade 2.5	Dynamically balanced with grade 2.5	
Wave form distortion	No load < 1.8 %, non distorting balanced linear load < 5 %	No load < 1.5 %, non distorting balanced linear load < 3 %	No load < 1.8 %, non distorting balanced linear load < 5 %	No load < 1.5 %, non distorting balanced linear load < 5 %	
Total Harmonic Factor	Better than 2%	Better than 2%	Better than 2%	Better than 2%	

\* Refer to Factory for 3.3/\*6.6 KV & Alternator frame

# **Conformance Standards**

IS/IEC 60034-1, BS 5000, IS 1460, ISO 8528, IS 13018, ISO 3046, ISO 9001

# **Rating Definitions**

# Standby Power (SP):


Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source, for maximum of 500 hours per year. Standby Power (SP) is in accordance with ISO 8528.

• Fuel consumption data is based on diesel having specific gravity of 0.85 and conforming to IS:1460

• Fuel consumption tolerance is +5%

Genset Model	RatingRating (kVA)	Length (mm)	Width (mm)	Height (mm)	Weight (kgs.) (Wet)	Std. Fuel Tank Capacity (Ltrs - External)
C2250D5S	2250 kVA	5950	2594	3304	17547	990
C2500D5S	2500 kVA	6175	2494	3115	16546	990

# **Typical Diesel Genset Dimensions\***





#### **Cummins Power System Offices**

Bengaluru:	Tel.: (080) 2325 9161 / 63, 2325 9165 / 67 Fax: (080) 2325 9164
Chandigarh:	Tel.: (0172) 224 0371-73 Fax: (0172) 224 0372
Chennai:	Tel.: (044) 2446 8110 / 2446 8113 Fax: (044) 2491 1120
Gurgaon:	Tel.: (0124) 391 0900-01 Fax : (0124) 391 0916
Hyderabad:	Tel.: (040) 2340 9970 / 2340 9980 Fax. (040) 2340 9990
Jaipur:	Tel.: (0141) 236 4944 Fax: (0141) 403 8794
Kolkata:	Tel.: (033) 2287 8065 / 2287 2481 Fax: (033) 2290 3839
Lucknow:	Tel.: (0522) 230 5049 / 230 5059 Fax: (0522) 230 5035
Mohali:	Tel.: (0172) 224 0371 / 72 / 73 Fax: (0172) 224 0371 / 72 / 73
Vadodara:	Tel.: (0265) 233 0627 / 3053627 Fax: (0265) 234 0623





"Our energy working for you."

Cummins is registered trademarks of Cummins Inc. Specifications are subject to change without notice. PSBU/029/QSK 60-2250-2500 kVA Standby//HD/MP/Revision-2 (22/07/2019)



#### Cummins India Limited Power Systems Business Cummins India Office Campus Tower-A, 8<sup>th</sup> Floor, S. No. 21, Balewadi, Pune – 411 045 (India)

Email: cpgindia@cummins.com www.cumminsindia.com