


# Diesel Generator Set QSB5.9 Series

140-160 kVA, 112-128 kWe Prime



## Latest Technology Product with Global Cummins® Platform

- The Cummins® QSB5.9 series heavy-duty engine and world class Stamford alternator powered diesel generator set
- Class defining Quantum engine technology with fully integrated subsystems
- Full Authority Electronic Engine
- Advanced in-cylinder technology to meet latest emission norms without any after-treatment device
- Smart aesthetic and superior finish
- Compact in size with optimum power to weight ratio

#### **Environment Friendly Power**

- Class defining technology engine is designed to meet stringent exhaust emission tests as per revised MoEF norms, thus offering environment friendly power
- The Cummins® diesel generator sets are available with the lowest noise levels in its range

## **Lowest Operating Cost and Comprehensive Warranty**

- Highly reliable and durable product
- All elements are designed to work together to maximize efficiency even at part loads, offering the advantage of lowest operating costs.
- 500 Hours/ 1 Year service interval
- Industry acknowledged best-in-class comprehensive warranty on the entire package including rubber components

#### **Single Source Power Assurance**

- All the major components the engine, alternator, control system and canopy are designed, manufactured and tested by Cummins India.
- Best and largest customer support network in India, capable of providing round-the-clock service and spares support
- All these things put together, Cummins<sup>®</sup> offers you SINGLE SOURCE POWER ASSURANCE

#### **Engine**

- Cummins® QSB5.9 series, 6 cylinder, in-line 4 stroke, radiator cooled engine
- Full Authority Electronic Engine
- Well designed air handling system with
  - Dry type, Heavy duty, Replaceable paper element air cleaner with restriction indicator
  - Air to air aftercooling
  - Optimised turbocharger for increased altitude capabilities
- Best in class fuel economy with
  - Bosch HPCR fuel system with A1 class electronic governing
  - Dual fuel filter system: Pre filter including water separator and Water In Fuel (WIF) sensor and main filter
- Standard integral set-mounted radiator system, designed and tested for 50°C ambient temperature
- Full flow spin on lube oil filter
- Plate type lube oil cooler
- First fill of lube oil and coolant
- Electrical starter motor with soft start engagement feature
- Battery charging alternator
- 2x12 V DC batteries



#### Alternator

- STAMFORD S3L1D alternator frames from Cummins Generator Technologies
- Brushless type, screen protected, revolving field, self excited alternator conforming to IS/IEC 60034-1
- 3 Phase dedicated winding with 6 terminals brought out for connection
- Better motor starting capability
- Best in class efficiency
- Compact design with sealed bearings for longer life and lesser maintenance
- Impregnation on all wound components for better mechanical strength
- Digital Automatic Voltage Regulator

#### **PS0602 Features**

Cummins® PowerStart™ PS0602 control is a microprocessor based generator set monitoring, metering and control system with LCD display designed to meet the demands of today's engine driven generator sets



- AMF Functionality
- Electronic Governing
- CAN (J1939) Compatible
- Sync Compatible (Capable to accept external speed signal from 3rd party sync controller)
- Intuitive operator interface which includes LED backlit 128X64 pixel graphic display with tactile feel soft- switches & generator set status LED lamps.
- Remote start-stop
- Engine Metering: Oil pressure, Engine temperature, battery voltage, Engine running hours
- AC Alternator Metering: L-L Voltage and L-N Voltage,
- Current (phase and total), kVA (phase and total), Frequency, kWH, kW and kVA (phase and total), PF, Utility Voltage and Freq.
- Engine Protection: Low lube oil pressure, High/ Low coolant temperature, Battery Over/ Under/ Weak Volts, Fail to Crank/ Start, Sensor failure, Cranking lockout.
- AC Alternator Protection: Over/ Under Voltage, Over/ Under Frequency, Loss of AC Sensing, Over speed, Over Current.
- Data Logging: Engine Hours, Control Hours and upto 5 recent fault codes
- Configurable glow plug control
- 12/24 Volt DC operation
- Sleepmode
- Mod bus interface (RS485 RTU)
- In Power compatible (PC based service tool)
- Certifications meets the requirement of relevant ISO, EN, Mil Std. and CE standards Maintenance due alarm based on Engine Run Time and due date
- Exerciser scheduler

#### Silencer

 Hospital grade silencer suitably optimized to meet stringent noise emission standards laid down by MoEF / CPCB

#### **Mounting Arrangement**

- Engine and alternator are mounted on a common MS fabricated base frame with AVM pads.
- Base frame with integral fuel tank is provided with drain plug, air vent, inlet and outlet connection, level indicator and provision for cleaning

#### **Optional**

- Engine: Coolant heater.
- Alternator: PMG.
- Control Panel: PC3.3,

Bargraph For PC3.3 Panel with kW, Power factor, Frequency, Current, Voltage Microprocessor / relay based AMF

#### **Acoustic Enclosure**

- Specially designed to meet stringent MoEF / CPCB norms of 75 dBA@1mtr at 75% load under free field conditions
- The acoustic enclosure is made of CRCA sheets in munsel green shade and a structural/ sheet metal base frame painted in black
- High quality noise absorbant and fire-retardant grade acoustic insulation material (PU Foam) complying to IS 8183
- Two point lifting for easy handling at customer site
- Designed to have optimum serviceability

- Air inlet louvers specially designed to operate at rated load
- Made on special purpose CNC machines for consistency in quality and workmanship
- 11 tank pretreatment process and UV resistant powder coating of all parts to withstand extreme environment

C160D5P

- Use of special hardware for longer life
- Flush styling no projections
- Fluid drains for lube oil and fuel
- Fuel filling arrangement inside the enclosure

#### **Technical Data**

Model

#### **Generator Set Specification**

****	1			
Duty	Prime	Prime		
Power Rating kVA / kWe	140/112	160/128		
No. of Phases	3	3		
Output Voltage and Frequency (V and Hz)	415 V, 50 Hz	415 V, 50 Hz		
Power Factor	0.8 (lagging)	0.8 (lagging)		
Current (A)	195	223		
RPM	1500	1500		
Engine Specification:	(NE)			
Make	Cummins®	Cummins®		
Model	QSB5.9-G1	QSB5.9-G2		
MoEF Certified Power (bhp)	184	206		
Required Power for Rated kVA (bhp)	175	197		
Cooling	Liquid Cooled (EG Compleat 50:50)	Liquid Cooled (EG Compleat 50:50)		
Aspiration	Turbocharged, Charge Air Cooled	Turbocharged, Charge Air Cooled		
No. of cylinders	6, In-line	6, In-line		
Bore (mm) x Stroke (mm)	102 x 120	102 x 120		
Compression ratio	16.5:1	16.5:1		
Displacement (litre)	5.88	5.88		
Fuel	High Speed Diesel	High Speed Diesel		
Fuel consumption @75% load	25.92	29.93		
with radiator and fan* (litre/hr)				
Fuel consumption @100% load	31.91	35.95		
with radiator and fan* (litre/hr)	100 0500 5 00	100 0500 5 00		
Performance class of generator set	ISO 8528-5 G2	ISO 8528-5 G2		
Starting system	24 V DC Electrical	24 V DC Electrical		
Lube oil specification	CI4+ 15W40	Cl4+ 15W40		
Lube oil sump capacity, High-Low level (litre)	14.2- 12.3	14.2- 12.3		
Total lubrication system capacity (litre)	15.7	15.7		
Total coolant capacity (litre)	25.6	25.6		
Exhaust pipe size (inch)	4	4		
Total wet weight (Engine+Radiator)## (kg)	552	552		
Length x Width x Height (Engine) (mm)	1066 x 642 x 1029	029 1066 x 642 x 1029		
Mean piston speed (m/s)	6	6		
Combustion air intake @100% load (±5%) (cfm)	382	400		
Exhaust Temperature (°C)	496	522		
Alternator Specification:				

C140D5P

Alternator Specification:	also the state of		
Make	STAMFORD (CGT)	STAMFORD (CGT)	
Alternator Frame	S3L1D-E	S3L1D-F	
Enclosure	IP 23	IP 23	
Voltage regulation	±0.5%	±0.5%	
Class of Insulation	H Class	H class	
Winding Pitch	2/3 Pitch	2/3 Pitch	
Stator Winding	Double layer Concentric	Double layer Concentric	
Rotor	Dynamically Balanced	Dynamically Balanced	
Waveform distortion / Total Harmonic Distortion	No load < 1.5 %, Non distorting	No load < 1.5 %, Non distorting	
	balanced linear load < 5 %	balanced linear load < 5 %	
Maximum Unbalanced Load across phases#	less than or equal to 25%	less than or equal to 25%	
Telephonic Harmonic factor	< 2%	< 2%	

<sup>\*</sup>Fuel consumption data is based on diesel having specific gravity of 0.85 and conforming to IS:1460. Fuel consumption tolerance is +5% #With the condition that none of the phases exceeds its rated current

### **Rating Definitions**

Prime Power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO

#### **Conformance Standards**

■ IS/IEC 60034-1

■ IS 1460

■ ISO 8528

■ ISO 3046

■ ISO 9001


■ IS 13018

#### **Typical Enclosed Genset Dimensions**

Genset Model	Rating (kVA)	Length (mm)	Width (mm)	Height (mm)	Wet Weight## (kg)	Standard Fuel tank Capacity (litre)
C140D5P	140	4000	1150	1850	2528	290
C160D5P	160	4000	1150	1850	2528	290

<sup>\*\*\*</sup>Approximate Weight





Authorised Representative

#### **Cummins Power Generation Offices**

Bengaluru: Tel.: (080) 2325 9161 / 63, 2325 9165 / 67

Fax: (080) 2325 9164

Tel.: (0172) 224 0371-73 Fax: (0172) 224 0372 Chandigarh:

Chennai: Tel.: (044) 2446 8110 / 2446 8113

Fax: (044) 2491 1120 Tel.: (0124) 391 0900-01 Fax: (0124) 391 0916

Gurgaon:

Hyderabad: Tel.: (040) 2340 9970 / 2340 9980 Fax: (040) 2340 9990

Tel.: (0141) 236 4944 Fax: (0141) 403 8794 Jaipur:

Tel.: (033) 2287 8065 / 2287 2481 Kolkata: Fax: (033) 2290 3839

Tel.: (0522) 230 5049 / 230 5059 Lucknow:

Fax: (0522) 230 5035

Tel.: (0172) 224 0371 / 72 / 73 Fax: (0172) 224 0371 / 72 / 73 Mohali:

Tel.: (0265) 233 0627 / 3053627 Fax: (0265) 234 0623 Vadodara:



https://www.facebook.com/cumminsindiaofficial/





https://www.instagram.com/cumminsindiaofficial/



https://www.cummins.com/en/in/products/diesel-generators





**Cummins India Limited** Power Systems Business Unit Cummins India Office Campus Tower-A, 8th Floor, S. No. 21, Balewadi, Pune - 411 045 (India)

Phone: +91 20 6706 7000 Toll Free: 1800-210-2525\* Email: saeindia@cummins.com www.cummins.com