



Europe model range

50 Hz range

Model name	Standby rating		Prime rating		DCC rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure	Emissions	Sound enclosure
	kVA	kWe	kVA	kWe	kVA	kWe							
C17D5	16.5	13	15	12					X2.5-G2	S0L1-P1	PS0600		Yes
C22D5	18	17	20	16					X2.5-G2	S0L2-G1	PS0600		Yes
C22D5Q	22	18	20	16					X2.5-G2	S0L2-G1	PS0600		Yes
C28D5	27.5	22	25	20					X2.5-G2	S0L2-M1	PS0600		Yes
C44D5e	44	35	40	32					B3.3-G14	UCI224C	PS0600	EU Stage IIIA	Yes
C55D5EQ	55	44	50	40					4BTAA3.3-G14	UC 224 D	PS0600	EU Stage IIIA	Yes
C55D5e	55	44	50	40					B3.3-G14	UCI224D	PS0600	EU Stage IIIA	Yes
C66D5EQ	66	53	60	48					4BTAA3.3-G14	UC 224 F	PS0600	EU Stage IIIA	Yes
C330D5EQ	330	264	300	240					QSL9-G7	HC1444D	PC 1.2	EU Stage IIIA	Yes
C450D5Q	450	360	409	327					QSG12-G4	S4L1D-G41	PC 1.2		Yes
C550D5QB	550	440	500	400					M15-G8	S5L1S-D4	PC 1.2		Yes
C55D5e	55	44	50	40					B3.3-G14	UCI224D	PS0600	EU Stage IIIA	Yes
C66D5EQ	66	53	60	48					4BTAA3.3-G14	UC 224 F	PS0600	EU Stage IIIA	Yes
C66D5e	66	53	60	48					B3.3-G14	UCI224F	PS0600		Yes
C90D5	90	72	82	65					6BTA5.9-G5	UCI224G	PC 1.2		Yes
C110D5Q	110	88	100	80					6BTA5.9-G5	UCI274C	PS0600		Yes
C110D5	110	88	100	80					6BTA5.9-G5	UCI274C	PC 1.2		Yes
C150D5	150	120	136	109					6BTAA5.9-G6	UCI274E	PC 1.2		Yes
C170D5Q	170	136	155	124					6BTAA5.9-G7	UCI274F	PS0600		Yes
C170D5	170	136	155	124					6BTAA5.9-G7	UCI274F	PC 1.2		Yes
C175D5e	175	140	160	128					QSB7-G5	UCI274F	PC 1.2	EU Stage IIIA	
C200D5E	200	160	182	146					QSB7-G5	UCI274H	PC 1.2	EU Stage IIIA	

EUROPE 50 Hz RANGE

Model name	Standby rating		Prime rating		DCC rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure	Emissions	Sound enclosure
	kVA	kWe	kVA	kWe	kVA	kWe							
C220D5EQ	220	176	200	160					QSB7-G5	UCI274H	PC 1.2	EU Stage IIIA	Yes
C220D5e	220	176	200	160					QSB7-G5	UCI274H	PC 1.2	EU Stage IIIA	Yes
C275D5EQ	275	220	250	200					QSL9-G7	UCDI274K	PC 1.2	EU Stage IIIA	Yes
C275D5	275	220	250	200					QSL9-G5	UCDI274K	PC 1.2		Yes
C275D5e	275	220	250	200					QSL9-G7	HCI4D	PC 1.2	EU Stage IIIA	Yes
C300D5	300	240	275	220					QSL9-G5	HCI4D	PC 1.2		Yes
C300D5e	300	240	275	220					QSL9-G7	HCI4D	PC 1.2	EU Stage IIIA	Yes
C330D5EQ	330	264	300	240					QSL9-G7	HCI444D	PC 1.2	EU Stage IIIA	Yes
C330D5	330	264	300	240					QSL9-G5	HCI4D	PC 1.2		Yes
C330D5e	330	264	300	240					QSL9-G7	HCI4D	PC 1.2	EU Stage IIIA	Yes
C400D5	400	320	360	288					QSG12-G3	S4L1D-F41	PC 2.2		Yes
C400D5eB	400	320	360	288					QSZ13-G7	S5L1D-C41	PC 2.2	EU Stage IIIA	Yes
C450D5Q	450	360	409	327					QSG12-G4	S4L1D-G41	PC 2.2		Yes
C450D5	450	360	409	327					QSG12-G4	S4L1D-G41	PC 2.2		Yes
C450D5eB	450	360	409	327					QSZ13-G7	S5L1D-C41	PC 2.2	EU Stage IIIA	Yes
C500D5	500	400	455	364					QSZ13-G5	S5L1D-D41	PC 2.2	EU Stage II	Yes
C550D5QB	550	440	500	400					M15-G8	S5L1S-D4	PC 2.2		Yes
C550D5	550	440	500	400					QSZ13-G10	S5L1D-D41	PC 2.2		Yes
C640D5	640	512	582	466					KTA19-G6	HC5E	PC 1.2		
C700D5	706	565	640	512	640	512			VTA28-G5	HC5F	PC 3.3		
C825D5	825	660	750	600	750	600			QSK23-G3	S6L1C4	PC 3.3		Yes
C825D5E	825	660	750	600	750	600			QSK23-G9	S6L1C4	PC 3.3	EPA Tier 2	Yes
C825D5A	825	660	750	600	750	600			VTA28-G6	S6L1C4	PC 3.3		
C900D5	900	720	820	656	820	656			QSK23-G3	S6L1D4	PC 3.3		Yes

EUROPE 50 Hz RANGE

Model name	Standby rating		Prime rating		DCC rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure	Emissions	Sound enclosure
	kVA	kWe	kVA	kWe	kVA	kWe							
C900D5E	900	720	820	656	820	656			QSK23-G9	S6L1D4	PC 3.3	EPA Tier 2	Yes
C1000D5B	1000	800	900	720	900	720			KTA38-G14	S6L1DE4	PC 3.3		Yes
C1100D5B	1132	906	1029	823	1029	823			KTA38-G14	S6L1DF4	PC 3.3		Yes
C1250D5AB	1250	1000	1125	900					KTA38-G9	S6L1DG41	PC 3.3		Yes
C1400D5	1400	1120	1250	1000	1250	1000			KTA50-G3	PI734B	PC 3.3		
C1675D5A	1675	1340	1500	1200	1500	1200			KTA50-GS8	PI734D	PC 3.3		
C1760D5	1760	1408	1600	1280	1600	1280			KTA50-G23	S7L1D-E4	PC 3.3		
C1875D5	1875	1500	1700	1360	1700	1360			KTA50-G23	S7L1D-F4	PC 3.3		
C1875D5E	1875	1500	1700	1360	1700	1360			QSK50-G15	S7L1D-F4	PC 3.3	EPA Tier 2	
C2000D5B	2000	1600	1800	1440	1800	1440			KTA50-G23	S7L1D-G4	PC 3.3		
C2000D5EB	2000	1600	1875	1500	1875	1500			QSK50-G16	S7L1D-G4	PC 3.3	EPA Tier 2	
C2000D5	2063	1650	1875	1500	1875	1500			QSK60-G3	PI734F	PC 3.3		
C2250D5	2250	1800	2000	1600	2000	1600			QSK60-G4	PI734G	PC 3.3		
C2250D5E	2250	1800	2000	1600					QSK50-G17	S7L1D-H4	PC 3.3	EPA Tier 2	
C2500D5A	2500	2000	2250	1800	2250	1800			QSK60-G8	LVS1804R	PC 3.3		
C2750D5BE	2750	2200	2500	2000	2500	2000			QSK60-G23	LVS1804W	PC 3.3	EPA Tier 2	
C3000D5	3000	2400	2750	2200	2750	2200	2475	1980	QSK78-G9/G24	MVSI804S	PC 3.3		
C3000D5e	3000	2400	2750	2200	2750	2200	2100	1680	QSK78-G23/ QSK78-G16	MVSI804S	PC 3.3	EPA Tier 2/ TA Luft 2g	
C3500D5	3500	2800	3125	2500	3125	2500	2750	2200	QSK95-G4	LVS1804W	PC 3.3		
C3500D5e	3500	2800	3125	2500	3125	2500	2750	2200	QSK95-G5/ QSK95-G10	LVS1804W	PC 3.3	EPA Tier 2/ TA Luft 2g	
C3750D5	3750	3000	3350	2680	3350	2680	3000	2400	QSK95-G4	LVS1804X	PC 3.3		
C3750D5e	3750	3000	3350	2680	3350	2680	3000	2400	QSK95-G10	LVS1804X	PC 3.3	EPA Tier 2	

* Specifications may change without notice



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

Bulletin 6614074 Produced in U.S.A. 3/25
©2025 Cummins Inc.