



North America model range

60 Hz range

Model name	Standby rating		Prime rating		DCC rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure
	kVA	kWe	kVA	kWe	kVA	kWe					
C10D6	12.5	10	11.4	9.1			D1703M	CA115-114	PC 1.1	EPA Tier 4I	Yes
C15D6	18.8	15	16.8	13.6			D1703M	CA115-L14	PC 1.1	EPA Tier 4I	Yes
C20D6	25	20	22.8	18.2			V2203M	CA115-L14	PC 1.1	EPA Tier 4I	Yes
C25D6	31.2	25	28.3	22.7			4BT3.3-G5	CA115-L14	PC 1.1	EPA Tier 3	Yes
C30D6	37.5	30	33.7	27			4BT3.3-G5	CA115-P14	PC 1.1	EPA Tier 3	Yes
C35D6	43.7	35	40	32			4BT3.3-G5	CA115-S14	PC 1.1	EPA Tier 3	Yes
C40D6	50	40	45	36			4BT3.3-G5	CA115-V14	PC 1.1	EPA Tier 3	Yes
C50D6	63	50	56	45			4BT3.3-G7	CA125-J14	PC 1.1	EPA Tier 3	Yes
C50D6C	63	50	56	45			QSB5-G13	UC2D	PC 1.1	EPA Tier 3	Yes
C60D6	75	60	67.5	54			4BT3.3-G7	CA125-L14	PC 1.1	EPA Tier 3	Yes
C60D6C	75	60	68	54			QSB5-G13	UC2E	PC 1.1	EPA Tier 3	Yes
C80D6C	100	80	90	72			QSB5-G13	UC3E	PC 1.1	EPA Tier 3	Yes
C100D6C	125	100	113	90			QSB5-G13	UC3D	PC 1.1	EPA Tier 3	Yes
C125D6C	156	125	141	112.5			QSB5-G6	UC3E	PC 1.1	EPA Tier 3	Yes
C125D6D	156	125	141	112.5			QSB7-G5	UC3E	PC 1.1	EPA Tier 3	Yes
C150D6D	187.5	150	168.7	135			QSB7-G5	UC3F	PC 1.1	EPA Tier 3	Yes
C175D6D	218.7	175	196.8	157.5			QSB7-G5	UC3H	PC 1.1	EPA Tier 3	Yes
C200D6D	250	200	225	180			QSB7-G5	UCD3J	PC 1.1	EPA Tier 3	Yes
DSHAD	288	230	263	210			QSL9-G2 NR3	UCD3J	PC 2.3	EPA Tier 3	Yes
DQDAA	313	250	281	225	513	410	QSL9-G7	HCI434F	PC 2.3	EPA Tier 3	Yes
DQDAB	344	275	313	250	569	455	QSL9-G7	HCI434F	PC 2.3	EPA Tier 3	Yes
C275D6D	343	275	312	250	681	545	QSL9-G9	S4L1S-F4	PCC 3300	EPA Tier 4	No
DQDAC	375	300	338	270	850	680	QSL9-G7	HCI434F	PC 2.3	EPA Tier 3	Yes
DFEJ	563	450	513	410	513	410	QSL9-G9	HC5D	PC 2.3	EPA Tier 2	Yes
DFEK	625	500	569	455	569	455	QSL9-G9	HC5E	PC 2.3	EPA Tier 2	Yes
DQCA	750	600	681	545	681	545	QSK23-G7	HC6G	PC 2.3	EPA Tier 2	Yes
DQCB	938	750	850	680	850	680	QSK23-G7	HC6G	PC 2.3	EPA Tier 2	Yes
DQFAA	938	750	850	680	850	680	QST30-G5	HC6G	PC 3.3	EPA Tier 2	Yes

NORTH AMERICA 60 Hz RANGE

Model name	Standby rating		Prime rating		DCC rating		Engine model	Standard alternator	Standard controller	Emissions certification	Sound enclosure
	kVA	kWe	kVA	kWe	kVA	kWe					
DQCC	1000	800	906	725	906	725	QSK23-G7	HC6G	PC 2.3	EPA Tier 2	Yes
DQFAB	1000	800	906	725	906	725	QST30-G5	HC6G	PC 3.3	EPA Tier 2	Yes
DQFAC	1125	900	1023	818	1023	818	QST30-G5	HC6H	PC 3.3	EPA Tier 2	Yes
DQFAD	1250	1000	1125	900	1125	900	QST30-G5	HC6K	PC 3.3	EPA Tier 2	Yes
DQFAH	1250	1000	1125	900	1125	900	QST30-G17	HC6K	PC 3.3	EPA Tier 4F	No
C1250D6E	1563	1250	1420	1136	1420	1136	QSK38-G17	S6L1D-H4	PC 3.3	EPA Tier 2	No
C1500D6E	1875	1500	1705	1364	1705	1364	QSK38-G18	S7L1D-C4	PC 3.3	EPA Tier 2	No
DQGAE	1563	1250	1419	1135	1419	1135	QSK50-G5	PI734B	PC 3.3	EPA Tier 2	No
DQGAF	1875	1500	1706	1365	1706	1365	QSK50-G5	PI734C	PC 3.3	EPA Tier 2	No
C1750D6E	2188	1750	2000	1600	2000	1600	QSK50-G24	S7L1D-F4	PC3.3	EPA Tier 2	No
C2000D6E	2500	2000	2281	1825	2281	1825	QSK50-G24/G25	S7L1D-G4	PC3.3	EPA Tier 2	No
DQKAB	2500	2000	2281	1825			QSK60-G6	PI734F	PC 3.3	EPA Tier 2	No
DQKAE	2500	2000	2281	1825	2281	1825	QSK60-G6	PI734F	PC 3.3	EPA Tier 2	No
DQKAF	2813	2250	2281	1825	2500	2000	QSK60-G14	PI734G	PC 3.3	EPA Tier 2	No
DQKAN	3125	2500			2813	2250	QSK60-G19	LVS1804X	PC 3.3	EPA Tier 2	No
DQLF	3438	2750	3125	2500	3125	2500	QSK78-G12	LVS1804S	PC 3.3	EPA Tier 2	No
C2750D6E	3438	2750	3125	2500	3125	2500	QSK78-G36	S9L1D-E4	PC 3.3	EPA Tier 2/ Low NOx Only	No
C3000D6EB	3750	3000	3438	2750	3438	2750	QSK78-G37	S9L1D-E4	PC 3.3	EPA Tier 2	No
C3000D6	3750	3000	3438	2750	3438	2750	QSK95-G2	LVS1804W	PC 3.3		No
C3000D6e	3750	3000	3438	2750	3438	2750	QSK95-G9	LVS1804W	PC 3.3	EPA Tier 2	No
C3250D6	4063	3250	3750	3000	3750	3000	QSK95-G2	LVS1804W	PC 3.3		No
C3250D6e	4063	3250	3750	3000	3750	3000	QSK95-G9	LVS1804W	PC 3.3	EPA Tier 2	No
C3500D6	4375	3500	3750	3000	4188	3350	QSK95-G2	LVS1804X	PC 3.3		No
C3500D6e	4375	3500	3750	3000	4188	3350	QSK95-G9	LVS1804X	PC 3.3	EPA Tier 2	No
C3500D5	3500	2800	3125	2500	3125	2500	QSK95-G4	LVS1804W	PC 3.3		No
C3500D5e	3500	2800	3125	2500	3125	2500	QSK95-G5/ G10	LVS1804W	PC 3.3	EPA Tier 2/ 2g Low NOx	No
C3750D5	3750	3000	3350	2680	3350	2680	QSK95-G4	LVS1804X	PC 3.3		No
C3750D5e	3750	3000	3350	2680	3350	2680	QSK95-G10	LVS1804X	PC 3.3	EPA Tier 2	No

* Specifications may change without notice