

# Application and Code Considerations for Specifying Generator Set Fuel Sources

**PowerHour** webinar series for consulting engineers  
Experts you trust. Excellence you count on.

February 18, 2021 11:00 PST / 14:00 EST

*(1PDH issued by Cummins)*

# Welcome!

Cummins PowerHour webinar series is designed to help our engineer partners to...

- Keep up to date on products, technology, and codes and standards development
- Interact with Cummins experts and gain access to ongoing technical support
- Participate at your convenience, live or on-demand
- Earn Professional Development Hours (PDH)

## Technical tips:

- Audio is available through teleconference or Zoom application.
- Attendees are in “listen only” mode throughout the event.
- Use the Zoom Q&A Panel to submit questions, comments, and feedback throughout the event. Time is allotted at the end of the PowerHour to address Q&A.
- If the audio connection is lost, disconnected or experiences intermittent connectivity issues, please check your audio connection through the "Join Audio" or "Audio Connectivity" button at the bottom left of the Zoom application.
- Report technical issues using the Zoom Q&A Panel.



# Meet Your Panelists

## Cummins Presenter & Panelists



Mark Taylor  
Technical Marketing Specialist  
Cummins Inc.



Scott Thomas  
Director - Sales Application  
Engineering  
Cummins Inc.



Earnest Glaser  
Senior Sales Application  
Engineer  
Cummins Inc.



Michael Sanford  
Product Strategy and Sales  
Enablement Leader  
Cummins Inc.

## Cummins Facilitator:

### Your local Cummins contacts:

- AZ, ID, NM, NV: Carl Knapp ([carl.knapp@cummins.com](mailto:carl.knapp@cummins.com))
- CO, MT, ND, UT, WY: Christopher Scott ([christopher.l.scott@cummins.com](mailto:christopher.l.scott@cummins.com))
- CA, WA, OR, AK, HI: Brian Pumphrey ([brian.pumphrey@cummins.com](mailto:brian.pumphrey@cummins.com))
- MA, ME, NH, RI, VT: Jim Howard ([james.howard@cummins.com](mailto:james.howard@cummins.com))
- CT, MD, NJ, NY : Charles Attisani ([charles.attisani@cummins.com](mailto:charles.attisani@cummins.com))
- Northern IL, MI, IA : John Kilinskis ([john.a.kilinskis@cummins.com](mailto:john.a.kilinskis@cummins.com))
- NE, SD, KS: Earnest Glaser ([earnest.a.glaser@cummins.com](mailto:earnest.a.glaser@cummins.com))
- IL, IN, KY, MO: Jeff Yates ([jeffrey.yates@cummins.com](mailto:jeffrey.yates@cummins.com))
- LA, MS, AL: Trina Casbon ([trina.casbon@cummins.com](mailto:trina.casbon@cummins.com))

- TX: Scott Thomas ([m.scott.thomas@cummins.com](mailto:m.scott.thomas@cummins.com))
- OK, AR: Wes Ruebman ([wes.ruebman@cummins.com](mailto:wes.ruebman@cummins.com))
- TN, GA: Mariano Rojas ([mariano.rojas@cummins.com](mailto:mariano.rojas@cummins.com))
- FL: Bob Kelly ([robert.kelly@cummins.com](mailto:robert.kelly@cummins.com))
- NC, SC, VA: Bill Morris ([william.morris@cummins.com](mailto:william.morris@cummins.com))
- Canada: Ian Lindquist ([ian.lindquist@cummins.com](mailto:ian.lindquist@cummins.com))
- PA, MD: Brian Cathcart ([brian.cathcart@cummins.com](mailto:brian.cathcart@cummins.com))
- DE, MN, ND, OH, WI, WV: Michael Munson ([michael.s.munson@cummins.com](mailto:michael.s.munson@cummins.com))

# Disclaimer

The views and opinions expressed in this course shall not be considered the official position of any regulatory organization and shall not be considered to be, nor be relied upon as, a Formal Interpretation.

Participants are encouraged to refer to the entire text of all referenced documents. In addition, when it doubt, reach out to the Authority Having Jurisdiction.




# Course Objectives

## **Application and Code Considerations for Specifying Generator Set Fuel Sources**

The installation of gaseous generator sets in a wide variety of applications continues to rise in North America while facility performance requirements, codes and standards are often most closely linked to their traditional diesel counterpart. As natural gas and propane fueled generator sets reach the market with “diesel-like” performance, it’s critical to understand how best to apply these products in order to maximize the value they provide. This course will provide an overview of gaseous generator set capabilities in various applications and will empower participants to recognize how to best apply gaseous generator sets to meet common performance and code requirements.

After completing this course, participants will be able to:

- Recognize performance requirements applicable to both diesel and gaseous generator sets.
- Describe key features and capabilities of gaseous generator sets.
- List key application considerations unique to gaseous generator set installations.



When compared to a diesel generator set, what are some of the differentiators unique to a natural gas (or propane) fueled generator set?

# Generator Set Fuel Sources

## Diesel and Gaseous Fuels

### Diesel Fuel


Power dense, high energy content

ULSD Diesel #2 ASTM D975

### Gaseous Fuel

Variable energy content

“Pipeline natural gas”



# Generator Set Fuel Sources

## Gaseous Fuels

Category	Also Known As	BTU
Conventional Natural Gas	Pipeline Gas, Standard Gas	High
	Associated Petroleum Gas (APG)	High
	Flare Gas, Field Gas	High
	Associated-Dissolved Gas (ADG)	High
	Wellhead Gas	High
Unconventional Natural Gas	Coal Bed Methane (CBM)	High
	Coal Mine Methane (CMM)	~Low
Biogas	Anaerobic Digester Gas (ADG)	Low
	Wastewater Treatment Plant Gas	Low
Syngas	Synthesis Gas, Pyrolysis Gas	Very Low
Industrial Gas	Town Gas	Very Low

**Spec Note** Conduct a fuel sample analysis, include the results in the specification and require manufacturers to provide documentation demonstrating capability with the on-site fuel.



# Generator Set Fuel Sources


## Gaseous Fuels - Methane Number

### Methane Index Number (MN)

- Defines likelihood of a fuel to auto-ignite
- Scale of 0-100
  - Higher MN may be less likely to auto-ignite (knock) and may be suitable for high power density applications.
  - Lower MN may be more likely to auto-ignite (knock) and may require power derate and/or timing changes.
- High quality pipeline natural gas is typically 80-90 MN.

### Methane number capability

Load (percent of rated)			
100%	90%	75%	50%
72	66	57	42



**Spec Note** Require generator set manufacturers to provide documentation indicating product performance at a specified Methane Number or range based on site fuel sample analysis.

# Generator Set Fuel Sources

## Gaseous Fuels - Methane Number

### Methane Index Number (MN)

- Defines likelihood of a fuel to auto-ignite
- Scale of 0-100
  - Higher MN may be less likely to auto-ignite (knock) and may be suitable for high power density applications.
  - Lower MN may be more likely to auto-ignite (knock) and may require power derate and/or timing changes.
- High quality pipeline natural gas is typically 80-90 MN.

Generator Set Data Sheet  
2000 kW Standby

**Model:** C2000 N6B  
**Frequency:** 60 Hz  
**Fuel Type:** Natural Gas MI 65+  
**Emissions NOx:** 1.0 g/bhp-hr  
**LT Water Inlet Temp:** 40 °C (104 °F)  
**HT Water Outlet Temp:** 92 °C (197 °F)

Measured sound performance data sheet:	MSP-2063
Prototype test summary data:	PTS-620
Remote radiator cooling outline:	A057J589

Fuel Consumption (ISO3046/1)	See Note	100% of rated load	90% of rated load	75% of rated load	50% of rated load
		4876 (16.65)	4149 (14.17)	2958 (10.1)	
		39.4%	38.6%	36.1%	
		37.1%	37.1%	34.6%	

Fuel	
Minimum gas supply pressure at DMV, bar (psi) <sup>7</sup>	0.24 (3.5)
Min methane index	65

Gross engine power output, kW (hp)	2113 (2833)
BMEP, bar (psi)	18.3 (265)
Bore, mm (in)	180 (7.09)
Stroke, mm (in)	200 (7.87)
Rated speed, rpm	1514
Piston speed, m/s (ft/min)	10 (1968)
Compression ratio	11.4:1
Lube oil capacity, L (qt)	582 (615)
Overspeed limit, rpm	1800
Regenerative power, kW	N/A
Full load lubricating oil consumption, L (qt) (0.3)	0.4 (0.3)

Fuel	
Minimum gas supply pressure at DMV, bar (psi) <sup>7</sup>	0.24 (3.5)
Min methane index	65

Our energy working for you.<sup>™</sup>  
©2019 Cummins Inc. | 0-7738 A001039 (02/19) | power.cummins.com

**Spec Note** Require generator set manufacturers to provide documentation indicating product performance at a specified Methane Number or range based on site fuel sample analysis.

# Generator Set Fuel Sources

## Rich Burn and Lean Burn Engines

	Rich Burn	Lean Burn
<b>Air Fuel Ratio</b>	~14.6 : 1	~25 : 1
<b>Excess Air (O<sub>2</sub>)</b>	0.2 to 0.8%	>4%
<b>Typical Application</b>	Fast start, large block loads	High efficiency, continuous operation, ramping load
<b>Emissions</b>	Aftertreatment may be required to reduce NO <sub>x</sub> and CO	Can often meet emissions requirements without aftertreatment

# Generator Set Fuel Sources

## Rich Burn and Lean Burn Engines

	Rich Burn	Lean Burn
<b>Air Fuel Ratio</b>	~14.6 : 1	~25 : 1
<b>Excess Air (O<sub>2</sub>)</b>	0.2 to 0.8%	>4%
<b>Typical Application</b>	Fast start, large block load	High efficiency, continuous operation, ramping load
<b>Emissions</b>	Aftertreatment may be required to reduce NO <sub>x</sub> and CO	Can often meet emissions requirements without aftertreatment

**Not Exclusive!**

**Spec Note** Specify project requirements critical to the generator set such as transient performance, motor starting capability or emissions limits. Avoid specifying “Rich Burn” or “Lean Burn” as it may drive unnecessary product requirements.

# Concept Check

When describing gaseous fuels, which of the following attributes are often used to describe fuel composition? (Choose one)

- a) Methane Number (MN)
- b) ASTM D975
- c) Air/Fuel Ratio
- d) Smell & odor

# Concept Check


When describing gaseous fuels, which of the following attributes are often used to describe fuel composition? Choose all that apply.

a) Methane Number (MN)

b) ASTM D975

c) Air/Fuel Ratio

d) Smell & odor



# Compliance to Codes and Standards

## Myths and Misconceptions

**MYTH:** “Gaseous generator sets may not be suitable for emergency or life safety applications.”

# Compliance to Codes and Standards


## Fuel Source for Emergency Systems

### NFPA 110-2019

5.1.1 The following energy sources shall be permitted to be used for the emergency power supply (EPS):

- (1) Liquid petroleum products...
- (2) Liquified petroleum gas...
- (3) Natural or synthetic gas

*Exception: For Level 1 installations in locations where the probability of interruption of off-site fuel supplies is high, on-site storage of an alternate energy source sufficient to allow full output of the EPSS to be delivered for the class specified shall be required, with the provision for automatic transfer from the primary energy source to the alternate energy source.*





# Compliance to Codes and Standards

## Fuel Source for Emergency Systems

### NFPA 110-2019

5.1.1 The following energy sources shall be permitted to be used for the emergency power supply (EPS):

- (1) Liquid petroleum products...
- (2) Liquefied petroleum gas...
- (3) Natural or synthetic gas

*Exception: For Level 1 installations in locations where the probability of interruption of off-site fuel supplies is high, on-site storage of an alternate energy source sufficient to allow full output of the EPSS to be delivered for the class specified shall be required, with the provision for automatic transfer from the primary energy source to the alternate energy source.*

### Natural Gas Council

Natural gas is a secure, reliable and resilient choice for customers

- Operational reliability
  - 2017 survey of 51 interstate pipelines – 99.97% of contractual commitments
  - Geographic dispersion of production reduces vulnerability to local weather
  - Transportation network interconnected, offering multiple pathways for rerouting
- Contractual continuity of service
  - Firm or interruptible contracts

# Compliance to Codes and Standards

## Fuel Source for Emergency Systems – Canada

### CSA 282 Emergency Electrical Power Supply for Buildings

#### 7.3.1 Minimum Quantity

A quantity of fuel sufficient for operating the engine under maximum site design load for at least 2h shall be maintained on site at all times...

#### 7.3.2 Health care facilities

...where a generator set is required for emergency power supply to essential electrical systems in conformance with CSA Z32, a fuel supply shall be maintained on site at all times...


#### 7.3.3 Off-site fuel supply

Notwithstanding Clause 7.3.1, when it can be demonstrated to the authority having jurisdiction that the reliability of the off-site utility fuel supply and the associated piping meets the requirements of Clause 7.3.1 for a continuous fuel supply, on-site storage might not be required.

# Compliance to Codes and Standards

## Fuel Source for Emergency Systems

Map of U.S. interstate and intrastate natural gas pipelines



Source: U.S. Energy Information Administration, *About U.S. Natural Gas Pipelines*

# Compliance to Codes and Standards

## Fuel Source for Emergency Systems

NFPA 70 – NEC Article:	Diesel	Gaseous (utility & on-site fuel source)	Gaseous (utility source only)
708 “COPS”	✓	✓	x*
700 “Life Safety”	✓	✓	✓*
701 “Legally Req’d”	✓	✓	✓
702 “Optional”	✓	✓	✓

\* Follow exemption process w/ AHJ per NFPA 110 Level 1 Systems

\*\* **NEC Article 708:** *Prime movers shall not be solely dependent on a public utility gas system for their fuel supply... Where internal combustion engines are used as the prime mover, an on-site fuel supply shall be provided...*

**Spec Note** Specify natural-gas fueled generator sets for emergency power systems where permitted by the local Authority Having Jurisdiction. (Perform a Hazard Analysis or Risk Assessment with the utility and AHJ early in the design phase.)

# Compliance to Codes and Standards

## Generator Set Ratings

ISO 8528: Defines application, ratings and performance of generator sets.

- Emergency Standby Power (ESP)
- Prime Rated Power (PRP)
- Limited Time Prime Power (LTP)
- Continuous Operating Power (COP)
- Data Center Power (DCP)

Any manufacturer can go above and beyond the ISO ratings definitions.




International Organization for Standardization.2018-02.ISO 8528-1.[www.iso.org](http://www.iso.org)

# Compliance to Codes and Standards

## Generator Set Ratings

### Emergency Standby Power (ESP)

- “Maximum power available during a variable electrical power sequence...for up to 200 h of operation per year”
- “The permissible average power output over 24 h of operation shall not exceed 70% of the ESP unless otherwise agreed by the RIC engine manufacturer”



**Spec Note** Specify ISO 8528 generator set power rating based on application requirements.

# Compliance to Codes and Standards

## NFPA 110 Type Requirements

### 4.3 Type.

The type defines the maximum time, in seconds, that the EPSS will permit the load terminals of the transfer switch to be without acceptable electrical power.

Table 4.1(b) Types of EPSSs

Designation	Power Restoration
Type U	Basically uninterruptible (UPS systems)
Type 10	10 sec
Type 60	60 sec
Type 120	120 sec
Type M	Manual stationary or nonautomatic — no time limit

# Compliance to Codes and Standards

## NFPA 110 Type Requirements

### 4.3 Type.

The type defines the maximum time, in seconds, that the EPSS will permit the load terminals of the transfer switch to be without acceptable electrical power.

Table 4.1(b) Types of EPSSs

Designation	Power Restoration
Type U	Basically uninterruptible (UPS systems)
Type 10	10 sec
Type 60	60 sec
Type 120	120 sec
Type M	Manual stationary or nonautomatic — no time limit

**Spec Note** Specify NFPA 110 Type requirement for Emergency Power Supply System based on application requirements and loads served.



# Compliance to Codes and Standards

## Starting Time Requirements – Canada

### CSA 282

#### 6.4 Power Supply Performance

6.4.1.b ...an emergency electrical power supply system shall be connected to life safety equipment ...and similar equipment essential for the operation of the emergency electrical power supply system within:

- i) 15 s of loss of normal power
- ii) 10 s of loss of normal power ... to vital loads of the essential electrical systems in conformance with **CSA Z32**

6.4.1.c Connections to firefighters' elevators, elevators serving floors above the first story in a high building, and smoke-venting fans may be delayed up to 60 s.

### CSA Z32

#### 6.2.1 Vital and delayed vital branches

...allow the vital and delayed vital branch loads to be transferred within 10 s and 2 min, respectively...

# Compliance to Codes and Standards

## Myths and Misconceptions

**MYTH:** “Gaseous generator sets may not be suitable for emergency or life safety applications.”

- ✓ Generator set manufacturers may be able to offer gaseous-fueled products that meet a wide range of applications.
- ✓ Natural gas may be acceptable to local authority having jurisdiction for life safety applications.
- ✓ Gaseous products may provide advantages over diesel products in applications due to fuel quality and logistics.

### Related Content

**NFPA 110 Time-to-Readiness Overview**  
[White Paper](#)  
[PowerHour](#)

Power topic #9002 | Technical information from Cummins Power Generation

## Application of lean-burn gas generator sets in standby service

> White paper  
By Tim Loehline, Technical Specialist—Electrical



Our energy working for you.™

Standby generator sets have been traditionally diesel engine driven and in limited cases stoichiometric (rich burn) natural gas or propane. These are popular choices because they provide a high level of performance and in the case of diesel especially, provide a high ratio of energy per unit volume of fuel stored at site.

More recently there is an increased interest in utilizing generator sets fueled by natural gas or renewable gaseous fuels. This trend is driven by a number of factors such as low exhaust emissions, higher efficiency, reduced carbon footprint, a desire to avoid diesel fuel storage issues, and potentially the use of renewable fuels.

Within Cummins Power Generation's line of products there is a range of reciprocating gaseous fueled generator sets that utilize lean-burn technology. lean-burn technology incorporates high air to fuel ratio and excess oxygen to gain overall output efficiency at greatly reduced NOx emissions.<sup>1</sup> These efficiency levels often exceed those of equivalent sized diesel products. Exhaust emissions are significantly lower than stoichiometric gas engines and greatly reduced from a diesel.

This paper addresses issues associated with lean-burn natural gas (LBNG) generator sets applied in standby service applications.

### Typical standby performance and ratings

A generator set in standby service as compared to other service such as peak shaving or prime power has unique requirements for starting and performance. Emergency codes such as NFPA 110 Standard for Emergency and Standby Power Systems<sup>®</sup> and CSA 282 Emergency Electrical Power Supply for Buildings have requirements for quick starting, 10 seconds for defined Emergency and some legally required systems. Certain other defined systems allow longer times to start and be ready to accept load, in some cases no time provisions are specified.

Load step acceptance capability is usually a critical factor in standby service. Switching from normal to emergency power sources through the use of large transfer switches high in the system usually result in single load steps that are a high percentage of the generator set rating. The generator set is not only expected to pick up this load step but to do it with relatively small voltage and frequency disturbance and to return to stability in a relatively short time. The practice of using smaller switching lower in the system mitigates this issue by dividing and sequencing load steps.

Another difference between standby and other service is typically the rating of a standby rated generator set is at or near its maximum capability in terms of engine horsepower and alternator kVA. One reason for this is to make full use of the hardware capability, providing adequate power in the smallest, lowest cost package available. The application designer must take this into account when considering total load and load step requirements.

<sup>1</sup> Reference Cummins Power Generation: Power topic #7009, Lean-burn engine technology increases efficiency, reduces NOx emissions. Keith Packham.

# Compliance to Codes and Standards

## Myths and Misconceptions

**MYTH:** “Because gaseous generator sets are **ALWAYS** cleaner than their diesel counterparts and they **NEVER** need exhaust aftertreatment.”

# Compliance to Codes and Standards

## Emissions Requirements

	Definition	How is it formed?	Diesel Engine	Gaseous Engine
NO <sub>x</sub>	Oxides of nitrogen	Forms at high in-cylinder temperatures, most prominent during high engine load.	✓	✓
HC	Over 100 different types of hydrocarbons	Product of incomplete combustion, most prominent during low engine load.	✓	✓
PM	Anything that is trapped on or condenses onto a filter	Most prominent during low load operation.	✓	
CO	Carbon Monoxide	Product of imperfect combustion, most prominent during low engine load.	✓	✓
SO <sub>x</sub>	Oxides of Sulfur	Product of combustion process when sulfur is present. Increases linearly with fuel consumption.	✓	

# Compliance to Codes and Standards

## Emissions Requirements

### US EPA New Source Performance Standards (NSPS)

#### Fuel Type

- Compression Ignition (Diesel) and Spark-Ignited (Gaseous)

#### Usage

- Stationary Emergency – operation when utility power is not available
- Stationary Non-Emergency – operation when utility power is available
- Non-road – mobile, non-propulsion without operational limitation (trailerized)

# Compliance to Codes and Standards

## Emissions Requirements

- Mandatory factory certification of rich burn propane engines
- Optional factory certification of all natural gas engines and lean burn propane engines
- If not factory certified, the owner/operator may be responsible for demonstrating compliance:

Engine Power	Maintenance plan and records, maintain/operate engine in a way to minimize emissions	Initial performance testing within 1 year of engine startup	Subsequent performance testing every 8,760 hours or 3 years, whichever comes first
< 100 hp	✓		
100-500 hp	✓	✓	
> 500 hp	✓	✓	✓

Reference: 40 CFR 60 Subpart JJJJ §60.4243 (a)(2)(i-iii)

**Spec Note** Require generator set vendor to provide documentation demonstrating compliance with specific emissions levels or engine certification.

# Compliance to Codes and Standards

## Emissions Requirements - Canada

Maintenance and NOx emission intensity limits for modern engines

<b>Regular-Use, Modern Engines</b> Engine Power	<b>NOx emission intensity limit</b> Ppmvd-15% / g/kWh	<b>Initial performance testing within 1 year of engine startup</b>	<b>Subsequent emissions checks every year</b>
75 - 375 kW	160 / 2.7	✓	
< 375 kW	160 / 2.7	✓	✓
<b>Low-Use, Modern Engines</b> Engine Power	<b>NOx emission intensity limit</b> Ppmvd-15% / g/kWh	<b>Initial performance testing within 1 year of engine startup</b>	<b>Subsequent emissions checks every year</b>
< 100 kW	160 / 2.7	None	None

# Compliance to Codes and Standards

## Emissions Requirements

### US EPA New Source Performance Standards (NSPS)

#### Fuel Type

- Compression Ignition (Diesel) and Spark-Ignited (Gaseous)

#### Usage

- Stationary Emergency – operation when utility power is not available
- Stationary Non-Emergency – operation when utility power is available
- Non-road – mobile, non-propulsion without operational limitation (trailerized)

### Local Air Quality Management Board

- May mandate stringent emissions limits requiring exhaust aftertreatment

**Spec Note** Require generator set vendor to provide documentation demonstrating compliance with specific emissions level requirement and applicable test methodology.



# Compliance to Codes and Standards

## Aftertreatment Systems

**Emissions requirements and usage may drive need for aftertreatment when applicable**

- Diesel Particulate Filter (DPF) reduces PM
- Selective Catalytic Reduction (SCR) reduces NOx
- Oxidation Catalyst (OxiCat) reduces CO, HC, some PM
- Three Way Catalyst reduces CO, HC, some PM



**Spec Note** Federal and local emissions requirements & usage are key specification inputs. Work with manufacturer to determine best approach for aftertreatment systems if necessary.

# Compliance to Codes and Standards

## Myths and Misconceptions

**MYTH:** “Because gaseous generator sets are cleaner than their diesel counterparts, they NEVER need exhaust aftertreatment.”

- ✓ Emissions limits may be based on a combination of Federal (US EPA), state (local air board) or customer-driven requirements.
- ✓ Application type (standby vs. nonroad, emergency vs. non-emergency) drive emissions limits.
- ✓ Engine manufacturers offer a wide range of products capable of meeting the most stringent requirements.
- ✓ In some cases, exhaust aftertreatment may be needed to achieve targeted emissions levels.

### Related Content

**EPA Emissions Regulations**  
[PowerHour](#)  
[White Paper](#)

# Concept Check

When specifying a generator set solution for an emergency power system, make sure to include... (choose all that apply)

- a) US EPA and other applicable emissions requirements
- b) ISO 8528 Power rating
- c) NFPA 110 Type requirement for system
- d) Engine air/fuel ratio

# Concept Check

When specifying a generator set solution for an emergency power system, make sure to include... (choose all that apply)

- a) US EPA and other applicable emissions requirements
- b) ISO 8528 Power rating
- c) NFPA 110 Type requirement for system
- d) Engine air/fuel ratio

# Installation Considerations

## Gaseous and Diesel Generator Sets

- Foundation, mounting and vibration isolation
- Exhaust systems
- Cooling and ventilation
- Service and maintenance access
- Starting system
- Sound considerations
- Remote monitoring solutions
- Housing and enclosure requirements



**Related  
Content**

**Generator Set Application Manual**  
[Application Guidelines T-030](#)

# Installation Considerations

## Fuel Source and Maintenance

### Maintenance of Diesel Fuel

Diesel fuel quality critical to equipment operation.

- Typical stable lifespan of diesel is 12 – 16 months in ideal conditions.
- Diesel sulfur content reduction (ULSD) limits fuel's anti-microbial properties.
- Bio-diesel blending may reduce fuel stability (up to 6 months), promotes water absorption and biomass growth.



**Spec Note** Require vendors to provide service and maintenance contracts that include fuel testing at least annually.

# Installation Considerations

## Fuel Source and Maintenance

### Maintenance of Gaseous Fuel

- Natural gas available through extensive pipeline network
- Avoid fuel transportation, handling, and storage issues
- No fuel tank cleaning required
- No fuel degradation over time
- Various fuels can be used



# Installation Considerations

## Fuel System Requirements

- Volume and pressure must be available at **RATED** load, not static pressure
- Be aware of fuel system pressure drop
- Provide a dedicated fuel line to generator set
- Accumulator or compressor to boost pressure, if necessary
- Consult generator set manufacturer for specific fuel system requirements.

### Fuel system

Gas supply pressure to engine inlet, bar (psi) <sup>8</sup>	0.2 (2.9)
Minimum methane index	62



**Spec Note** Require generator set vendors to provide documentation indicating engine minimum fuel pressure at rated load.




# Operational Considerations

## Operating Costs of NG-Fueled Generator Sets

### Natural Gas Operating Costs

- Natural gas generator set may be associated with greater capital costs (when compared to diesel) due to power density.
- Long term total cost of ownership indicates for diesel and natural gas products to be comparable in similar applications.
- Non-emergency operation (demand response, peaking, etc.) mandates Tier 4 levels for CI engines minimizing capital investment difference when compared to natural gas.




[www.eia.gov/naturalgas](http://www.eia.gov/naturalgas)

# Gaseous Generator Set Applications

## Myths and Misconceptions

**MYTH:** “Gaseous generator set transient performance and load acceptance is always worse than their diesel counterparts.”

- ✓ Engine control and fueling strategies continue to evolve.
- ✓ Rated load acceptance may not be suitable as a benchmark for product performance – transient performance limits must be based on application.
- ✓ Generator set sizing software may help to determine right-size generator set for a given application.



Power Suite™

Home Sizing Specifications Library Other Tools

Home > GenSize > GenSize Edit Project

GenSize Edit Project: [ Demo ]

Project Overview

Load Details: Light Load 1

Load Name	Light Load 1
Comments	
Type	Light Load
Light Type	Incandescent
Phase	Three
Project Voltage	277/480, Series Wye
Voltage	480
Running kW	200.00
Running kVA	200.00
Running PF	1.00
Running Amps	240.85
Starting kW	200.00
Starting kVA	200.00
Starting PF	1.00
Max. % Voltage Dip	35
Max. % Frequency Dip	10

GenSize on [powersuite.cummins.com](https://powersuite.cummins.com)

**Spec Note** Require generator set vendors to provide documentation from sizing software indicating compliance with transient and other project limits.

# Concept Check

When considering natural gas generator sets, which of these are NOT a key installation and operational differentiators when compared to diesel generator sets?

- a) Fuel system design requirements
- b) Fuel quality management
- c) Foundation, mounting and vibration
- d) Cost of operation

# Concept Check

When considering natural gas generator sets, which of these are NOT a key installation and operational differentiators when compared to diesel generator sets?

- a) Fuel system design requirements
- b) Fuel quality management
- c) Foundation, mounting and vibration**
- d) Cost of operation

# Gaseous Generator Sets

## Key Takeaways

**Natural gas fueled generator sets can provide...**

- ... reliable power generation in emergency and non-emergency applications
- ... emissions solutions that fit application requirements
- ... high efficiency options for prime and continuous operation
- ... compliance with appropriate codes and standards
- ... low or comparable cost of ownership
- ... strong performance capability comparable to diesel counterparts.



# Course Summary

## Considerations for Specifying Generator Set Fuel Sources

- Recognize performance requirements applicable to both diesel and gaseous generator sets.
- Describe key features and capabilities of gaseous generator sets.
- List key considerations unique to gaseous generator set installation.

## Key Takeaways

- Write specifications based on performance and application requirements such loads, transient limits, emissions, start-time and other code-driven requirements.
- Consider gaseous-fueled generator sets in applications where appropriate.

# Additional Resources

## Cummins White Papers

- [NFPA 110 Type 10 Starting Requirements for Generator Set Applications](#)
- [Understanding EPA NSPS Emissions Regulations for Stationary Spark-ignited Engines](#)
- [The Latest Evolution Of Distributed Energy Resources: Opportunity For Business Within The PJM](#)

## Cummins On-Demand Webinars

- [NFPA 110 Type 10 Requirements for Emergency Power Systems](#)
- [Gaseous Generator Set Installations and Case Studies](#)
- [Introduction to Generator Set Sizing Software](#)
- [EPA Emissions and Air Permitting](#)

POWER TOPIC 8003 | TECHNICAL INFORMATION FROM  
CUMMINS POWER GENERATION

## UNDERSTANDING EPA NSPS EMISSIONS REGULATIONS FOR STATIONARY SPARK-IGNITED ENGINES

White Paper  
Cummins Content

On June 12, 2006, the Environmental Protection Agency (EPA) proposed the New Source Performance Standards (NSPS) to regulate emissions from stationary spark-ignited engines and then finalized these standards on January 18th, 2008. Until the issuance of the SI NSPS, there were no Federal (US) emissions regulations for stationary natural gas or propane engines. Emissions regulations for stationary engines were usually governed by state and local permitting authorities and varied by the annual operating hours for the application.

This paper explains how the EPA NSPS apply to spark-ignited engines used in generator sets.

### IMPORTANT EPA DEFINITIONS

Stationary power sources such as diesel, natural gas or propane generator sets are regulated differently than non-road engine/generators such as rental or portable equipment. Additionally, emergency and non-emergency generator sets are regulated differently. Therefore, it is important to know how the EPA distinguishes emergency from non-emergency stationary engines and how the regulations for stationary applications differ from non-road engine regulations.



# Q&A

Please type your questions, comments and feedback in the **Zoom Q&A** window.

After the PowerHour, a complete list of questions and answers will be published on [powersuite.cummins.com](https://powersuite.cummins.com).

Please complete the brief survey after exiting the webinar!



Mark Taylor  
Technical Marketing Specialist  
Cummins Inc.



Scott Thomas  
Director - Sales Application  
Engineering  
Cummins Inc.



Earnest Glaser  
Senior Sales Application  
Engineer  
Cummins Inc.



Michael Sanford  
Product Strategy and Sales  
Enablement Leader  
Cummins Inc.

## Your local Cummins contacts:

- AZ, ID, NM, NV: Carl Knapp ([carl.knapp@cummins.com](mailto:carl.knapp@cummins.com))
- CO, MT, ND, UT, WY: Christopher Scott ([christopher.l.scott@cummins.com](mailto:christopher.l.scott@cummins.com))
- CA, WA, OR, AK, HI: Brian Pumphrey ([brian.pumphrey@cummins.com](mailto:brian.pumphrey@cummins.com))
- MA, ME, NH, RI, VT: Jim Howard ([james.howard@cummins.com](mailto:james.howard@cummins.com))
- CT, MD, NJ, NY : Charles Attisani ([charles.attisani@cummins.com](mailto:charles.attisani@cummins.com))
- Northern IL, MI, IA : John Kilinskis ([john.a.kilinskis@cummins.com](mailto:john.a.kilinskis@cummins.com))
- NE, SD, KS: Earnest Glaser ([earnest.a.glaser@cummins.com](mailto:earnest.a.glaser@cummins.com))
- IL, IN, KY, MO: Jeff Yates ([jeffrey.yates@cummins.com](mailto:jeffrey.yates@cummins.com))
- LA, MS, AL: Trina Casbon ([trina.casbon@cummins.com](mailto:trina.casbon@cummins.com))

- TX: Scott Thomas ([m.scott.thomas@cummins.com](mailto:m.scott.thomas@cummins.com))
- OK, AR: Wes Ruebman ([wes.ruebman@cummins.com](mailto:wes.ruebman@cummins.com))
- TN, GA: Mariano Rojas ([mariano.rojas@cummins.com](mailto:mariano.rojas@cummins.com))
- FL: Bob Kelly ([robert.kelly@cummins.com](mailto:robert.kelly@cummins.com))
- NC, SC, VA: Bill Morris ([william.morris@cummins.com](mailto:william.morris@cummins.com))
- Canada: Ian Lindquist ([ian.lindquist@cummins.com](mailto:ian.lindquist@cummins.com))
- PA, MD: Brian Cathcart ([brian.cathcart@cummins.com](mailto:brian.cathcart@cummins.com))
- DE, MN, ND, OH, WI, WV: Michael Munson ([michael.s.munson@cummins.com](mailto:michael.s.munson@cummins.com))



# Closing

Watch out for a follow-up email including:

- A link to the webinar recording and copy of the presentation
- A certificate issuing one professional development hour (1 PDH)

Visit [powersuite.cummins.com](https://powersuite.cummins.com) for:

- Sizing and specification development tools
- PowerHour webinar recordings, presentations and FAQ
- Additional Cummins continuing education programs

Check out our new podcast, [Brightest Bulbs](#):

- Learn about the latest innovations in energy and power
- Subscribe wherever you get your podcasts, or the link above

Visit [cummins.com/energy-iq](https://cummins.com/energy-iq) and sign-up for communications to:

- Receive energy insights
- Read about energy technologies and trends

## Upcoming PowerHour Webinars:

**March** – “Ask the Experts” for NFPA 110 Standard for Emergency and Standby Power Systems

